





T- Slot Base Plate square

Base Plates & Clamping



19582

BASE PLATES & CLAMPING ANGLES

Material

High tensile tool steel.

| Order No. | $w_1 \times l_1$ | w_2 ± 0.2 | w_3 | l_2 ± 0.2 | l_3 | l_4 | l_5 | h_1 ± 0.013 | d_1 | d_2 tol. h6 | Number of T-slots | Weight kg |
|--------------------|------------------|--------------------|-------|--------------------|-------|-------|-------|----------------------|-------|------------------|-------------------|--------------|
| 19582.W0700 | 400x400 | 100 | 60 | 100 | 50 | 65 | 175 | 150 | 12 | 20 | 5x5 | 61 |
| 19582.W0800 | 500x500 | 200 | 40 | 200 | 60 | 70 | 310 | 200 | 12 | 20 | 7x7 | 95 |
| 19582.W0900 | 630x630 | 200 | 35 | 200 | 70 | 70 | 340 | 200 | 16 | 25 | 9x9 | 152 |