


Locating Pad - Vee Type for screw jacks







15050

Material

Steel, hardened and blackened.

Tips

Can be used with screw jacks 15000 and

15300.

See technical pages for the table of screw jack suitability.

| Order No. | d_1 | d_2 | d ₃ | d ₄ min. | d ₄ max. | I_1 | l ₂ | I ₃ | Weight g |
|-------------|-------|-------|----------------|------------------------|------------------------|-------|----------------|----------------|-------------|
| 15050.W0045 | 45 | 42 | 12 | 10 | 50 | 23 | 8 | 3 | 120 |
| 15050.W0065 | 65 | 62 | 12 | 22 | 100 | 38 | 8 | 3 | 545 |





Clamping & Height Setting

Wixroyd Screw Jacks, **Locating and Support Elements**



15030 **Spherical**



15040 Pin Type



15050 Vee Type



15060 **Centering Pin**

SCREW JACKS



15070 Cylindrical



15080 Self-Aligning



15090 Pivot Ball



15000 Screw Jack



15042 **Locating Pad**



15062 **Centering Pad**



15002 Screw Jack



These screw and aligning jacks offer a broad range of applications. Due to their robust construction, the screw jacks function securely and precisely, with infinite adjustment even under heavy loads.

- Safe and reliable clamp supports for heights from 38 to 1250mm.
- Accurate and safe supporting and setting of any workpiece in various levels and heights.
- Aluminium screw jacks for delicate machine tables, surface plates and CMM tables.
- Magnetic screw jacks for horizontal and vertical supporting and setting.

Table of Suitability for Screw Jack Attachments

| Attachments | Suited to screw jacks with centering pin - plain bore | Suitable s | crew jack |
|-------------|---|------------|-----------|
| 15030 | | 15200 | 14130 |
| 15040 | | 15220 | 14140 |
| 15050 | | 15000 | 15300 |
| 15060 | Ø12 | 15000 | 15320 |
| 15070 | | 15100 | 15360 |
| 15080 | | 15120 | 15500 |
| 15090 | | | |

| Attachments | Suited to screw jacks with either / or centering pin - threaded | Suitable screw jack |
|-------------|---|-----------------------------|
| 15042 | M 12 | 15002.W0052 / W0070 / W0100 |
| 15062 | M 10 | 15320 15360 |
| 15062 | M 12 | 15002.W0052 / W0070 / W0100 |
| | , | |

| Attachments | Base thread | Suitable screw jack |
|-------------|-------------|---|
| 15042 | | 15000.W0052 / W0070 / W0100 |
| 15062 | M38 x 2 | 15000.W0052 / W0070 / W0100 15100 14140 |

