


Centering Pad for screw jacks







15060

Material

Steel, hardened and blackened.

Tips

Can be used with screw jacks 15000 and

15300.

See technical pages for the table of screw jack suitability.

Order No.	d_1	d_2	d ₃	I_1	I_2	l ₃	I_4	Weight
15060.W0145	45	12	35.8	19	3	8	8	120





Clamping & Height Setting

Wixroyd Screw Jacks, **Locating and Support Elements**



15030 **Spherical**



15040 Pin Type



15050 Vee Type



15060 **Centering Pin**

SCREW JACKS



15070 Cylindrical



15080 Self-Aligning



15090 Pivot Ball



15000 Screw Jack



15042 **Locating Pad**



15062 **Centering Pad**



15002 Screw Jack



These screw and aligning jacks offer a broad range of applications. Due to their robust construction, the screw jacks function securely and precisely, with infinite adjustment even under heavy loads.

- Safe and reliable clamp supports for heights from 38 to 1250mm.
- Accurate and safe supporting and setting of any workpiece in various levels and heights.
- Aluminium screw jacks for delicate machine tables, surface plates and CMM tables.
- Magnetic screw jacks for horizontal and vertical supporting and setting.

Table of Suitability for Screw Jack Attachments

Attachments	Suited to screw jacks with centering pin - plain bore	Suitable s	crew jack
15030		15200	14130
15040		15220	14140
15050		15000	15300
15060	Ø12	15000	15320
15070		15100	15360
15080		15120	15500
15090			

Attachments	Suited to screw jacks with either / or centering pin - threaded	Suitable screw jack
15042	M 12	15002.W0052 / W0070 / W0100
15062	M 10	15320 15360
15062	M 12	15002.W0052 / W0070 / W0100
	,	

Attachments	Base thread	Suitable screw jack
15042		15000.W0052 / W0070 / W0100
15062	M38 x 2	15000.W0052 / W0070 / W0100 15100 14140

