


Swivel Max. - Fixed Flow Nozzle

modular coolant system - max. 6,7 bar

Coolant Nozzles

COOLANT NOZZLES



Material

Body: acetal. Spray tip: aluminium.

Technical Notes

Max. temperature: 43°C.

Max. pressure: 6,7 bar. Please order body and tip separately.

Tips

For use with our Swivel Max. coolant nozzle system (20051 to 20059).

Order No.	Туре	d ₁	d ₂	d ₃	I_1
20055.W1150	Тір	9.1	1.6	1/4"UNF	10.2
20055.W2121	Tip	9.1	2.2	1/4"UNF	10.2
20055.W2122	Tip	9.1	3.0	1/4"UNF	10.2
20055.W2123	Tip	9.1	4.0	1/4"UNF	10.2
20055.W2124	Body	12.0	1/4"UNF	-	12.7





COOLANT NOZZLES

Horizontal Clamping

up to 2.2 tons



Clamping Torque



11040/CL2040					
Clamping Torque	Clamping Force				
N/m	Ν				
50	23000				
40	18000				
30	12500				
25	11500				
20	9500				



11070/CL2070				
Clamping Torque	Clamping Force			
N/m	Ν			
60	16500			
50	15000			
40	12000			
30	10000			
25	8000			
20	7000			



11081/CL2081					
Clamping Torque	Clamping Force				
N/m	Ν				
5	6600				
4.5	5500				
4	4900				



10940/CL0030					
Clamping Torque	Clamping Force				
N/m	Ν				
8.5	4000				
8	3800				
7	3400				
6	3000				
5	2500				
4	2000				







Coolant Nozzles



System pressure (bar)	0.35	0.7	1.4	2.0	2.8	4.1	5.5
Orifice diameter (mm)			Flow r	ate (litres/r	ninute)		
1.02	0.32	0.45	0.64	0.77	0.91	1.18	1.41
1.57	0.86	1.14	1.68	2	2.32	2.82	3.32
2.18	1.64	2.32	3.27	3.86	4.55	5.46	6.82
2.79	2.91	4.09	6.36	7.27	8.18	10	11.37
4.06	6.36	9.09	12.73	15.91	18.18	21.82	25.46
5.59	11.37	16.82	23.64	30.46	35.46	42.28	48.19
System pressure (bar)	6.9	10.3	13.8	20.7	34.5	69.0	103.5
Orifice diameter (mm)	Flow rate (litres/minute)						
1.02	1.59	1.86	2.09	2.77	4	5.46	6.36
1.57	3.64	4.55	5.46	6.82	9.55	13.64	17.28
2.18	7.73	9.09	10.46	12.73	16.82	23.64	28.64
2.79	14.09	16.37	18.64	23.64	29.55	40.46	49.55
4.06	28.19	34.55	41.37	49.1	63.65	90.01	110.47
5.59	53.64	65.46	75.01	89.1	114.56	161.39	197.75

What Flow Rate of Coolant is Required?

Choose a nozzle with an orifice size that matches your pump's capacity.

Select an orifice size too big and coolant pressure will drop off, an orifice size too small and an inadequate amount of coolant will reach the tool tip and can result in damage.

Note: Flow rates are based on water at 20°. Actual results may vary with fluid type, extension length and aiming angle.

To calculate the average coolant exit velocity (important in some grinding operations where it is often desirable to match or exceed the peripheral velocity of the wheel) refer to the formula below. Choose an orifice size that produces sufficient back pressure to achieve the desired velocity.

Calculating Coolant Velocity

- $V = \frac{(17.11 \times 10^{-5}) \times F}{(d \times 10^{-3})^2}$
- Where;
- V = Velocity in m/s
- $C = Constant of 17.11 \times 10^{-5}$
- F = Flow rate through orifice in litres/min (see table above)
- d = Orifice diameter (mm) from product tables

Choose a nozzle extension that suits your application. Short projections are more compact and less likely to be knocked out of position by swarf or vibration. Longer extensions are easier to aim, produce a more streamline or laminar flow and shoot further.

A Word About Coolant Pumps

Nozzle Extensions

The most common coolant pump on CNC machine tools is a single stage centrifugal pump, normally designed to move high volumes of water at low pressure (typically 0.2 to 1.4 bar). Multi-stage centrifugal pumps are capable of higher pressures (typically 1.4 to 14 bar) while still producing high flow rates. Positive displacement pumps are used for very high pressure applications up to 140 bar and are generally used with small diameter orifices due to their lower flow rates.







0333 207 4497

sales@wixroyd.com

20051 - 20059 Fixing Elements


Swival Max-Modular Coolant Nozzle System




An extremely versatile system with an incredible range of motion in each joint – 72° either side of centreline! It's compact design is ideal for tight spaces. Available with fixed or variable flow nozzles and interchangeable orifices rated to 6.7 bar maximum and available with threaded or spherical bases. Vibration resistant joints provide superior reliability in CNC lathe turrets where inertial forces are high.

Variations

Links swivel 72° either side of centreline enabling it to come full circle within a 45mm inscribed circle.








Applications

The Swival Max coolant nozzle system with fixed flow end nozzles is ideal for CNC lathes due to its compactness and flexibility.

Variable flow end nozzles enable infinite flow control from full shutoff to full flow with fingertip control. They are ideal for manual and CNC mills.













wixroyd.com



Swivel Max

Modular Coolant Nozzle System

20051 - 20059 Fixing Elements

COOLANT NOZZLES

An extremely versatile coolant nozzle system compatible with new and existing installations.

Build your flexible system for your application.

