




Modular Screw Jack Base

adjustable



Screw Jacks



15370.5

SCREW JACKS

Material

Steel, tempered, burnished.

Enables easy positioning on a machine table.

Technical Notes

Can be used on T-slots and grid plates.

Order No.	h_1	h_2	h_3	w_1	w_2	d_1	d_2	l_1	l_2	l_3	Weight g
15370.W0456	106	56	20	158.5	20	90	42.5	240	195	17	5652



With the modular screw jack your production becomes even more flexible and economical. When combined you can achieve a maximum height of 1620mm.

Benefits

- Maximum height of 1620mm.
- Quick set-up time.

The Elements

- 1 Bearing pads, 15374.W0075, 15374.W0175, 15374.W0275
- 2 Screw jack, 15370.W0040, 15372.W0023
- 3 Spacer, 15370.W0116, 15370.W0126, 15370.W0135
- 4 Base, 15370.W0236, 15370.W0356, 15370.W0456
- 5 Thread adapter 15374.W0016, 15374.W0020, 15374.W0024

