




Pressure Max. - Coolant Nozzles

straight - with tube - max. 100 bar



Coolant Nozzles



20103

COOLANT NOZZLES

Material

Stainless steel body, ball and tube.

Technical Notes

Max. temperature: 70°C.

Max. pressure: 100 bar.

symbol α / symbol is an angle of adjustment

either side of centre line.

Tips

Interchangeable spray tips available allowing the orifice diameter and extension length to be easily changed to suit the application.

A high velocity coolant stream increases productivity and tool life.

Also useful for low pressure applications where abrasive swarf can be a problem.

Order No.	Type	A/F ₁	d ₁	d ₂	l ₁	l ₂	l ₃	A/F ₂	α
20103.W0100	Metric Fine	7/16"	M10x1,25	1.0	6.4	9.5	9.2	3/8"	±34°
20103.W0101	Metric Fine	7/16"	M10x1,25	1.6	6.4	9.5	9.1	3/8"	±34°
20103.W1060	Metric Coarse	7/16"	M 6x1,00	1.0	6.4	9.5	7.6	3/8"	±34°
20103.W1061	Metric Coarse	7/16"	M 6x1,00	1.6	6.4	9.5	7.6	3/8"	±34°
20103.W1080	Metric Coarse	7/16"	M 8x1,25	1.0	6.4	9.5	8.4	3/8"	±34°
20103.W1081	Metric Coarse	7/16"	M 8x1,25	1.6	6.4	9.5	8.6	3/8"	±34°
20103.W1100	Metric Coarse	7/16"	M10x1,50	1.0	6.4	9.5	9.1	3/8"	±34°
20103.W1101	Metric Coarse	7/16"	M10x1,50	1.6	6.4	9.5	9.1	3/8"	±34°