
Extendable Workpiece Locators





17004.1

Material

Body and piston: steel (S45C), tempered and black oxide finish.

Crank shaft: steel (S45C), black oxide

Crank shaft: steel (S45C), black oxide finish.

Technical Notes

Can support heavy workpieces made from

steel or cast iron. No tools needed. The handle position is freely adjustable. The handle can be easily changed to act in a clockwise or anti clockwise direction. Different locating pins can be mounted depending on workpiece's locating holes. The piston stays locked when it is fully

extended or retracted until the handle is operated again.

Order No.	h_1	h ₂	d_1	d ₂ tol. g6	d_3	d ₄ tol. G	d ₅	d_6	d ₇	d ₈	Weight
17004.W0008	48	12	50	28	20	8	38	M 5	M 4x5	M 6x12	590
17004.W0012	61	14	65	42	30	12	52	M 6	M 5x8	M 8x7	1310
Order No.	h ₃	h ₄	h ₅	h ₆	l ₁	r_1	Stroke s ₁	Allowable	e handle load N	Workpiece weight kg max.	
17004.W0008	22	27	14	5	65.0	40	12	170		250	
17004.W0012	26	31	16	6	87.5	65	15		210	300	

