





17100

Material

Steel, case-hardened and precision ground in pairs.

Technical Notes

DIN6364 P. Tolerances:
 h_1 (height) pair tolerance $tp2 =$ to IT5.

w_1 (width) pair tolerance $tp1 =$ to IT5.
 Other dimensions to ISO 2768m.

Order No.	h_1	l_1	Pair tolerance $tp1$ w_1	Pair tolerance $tp2$ h_1	Standard tolerance h_1	Standard tolerance w_1	w_1	Weight/pair g
17100.W0008	8	63	0.004	0.006	$\pm 0,2$	$\pm 0,1$	2.5	20
17100.W0010	10	63	0.005	0.006	$\pm 0,2$	$\pm 0,1$	3.2	30
17100.W0012	12	63	0.005	0.008	$\pm 0,2$	$\pm 0,1$	4.0	45
17100.W0013	12	100	0.005	0.008	$\pm 0,2$	$\pm 0,1$	4.0	75
17100.W0016	16	63	0.005	0.008	$\pm 0,2$	$\pm 0,1$	5.0	80
17100.W0017	16	100	0.005	0.008	$\pm 0,2$	$\pm 0,1$	5.0	125
17100.W0020	20	63	0.006	0.009	$\pm 0,2$	$\pm 0,2$	6.3	125
17100.W0021	20	100	0.006	0.009	$\pm 0,2$	$\pm 0,2$	6.3	200
17100.W0025	25	100	0.006	0.009	$\pm 0,2$	$\pm 0,2$	8.0	315
17100.W0026	25	160	0.006	0.009	$\pm 0,2$	$\pm 0,2$	8.0	500
17100.W0032	32	100	0.006	0.011	$\pm 0,3$	$\pm 0,2$	10.0	500
17100.W0033	32	160	0.006	0.011	$\pm 0,3$	$\pm 0,2$	10.0	800
17100.W0040	40	100	0.008	0.011	$\pm 0,3$	$\pm 0,2$	12.0	750
17100.W0041	40	160	0.008	0.011	$\pm 0,3$	$\pm 0,2$	12.0	1200
17100.W0050	50	160	0.008	0.011	$\pm 0,3$	$\pm 0,2$	16.0	2000
17100.W0063	63	160	0.009	0.013	$\pm 0,3$	$\pm 0,2$	20.0	3170
17100.W0064	63	250	0.009	0.013	$\pm 0,3$	$\pm 0,2$	20.0	4950
17100.W0080	80	250	0.009	0.013	$\pm 0,3$	$\pm 0,2$	25.0	7900
17100.W0100	100	250	0.011	0.015	$\pm 0,3$	$\pm 0,3$	32.0	12680
17100.W0101	100	400	0.011	0.015	$\pm 0,3$	$\pm 0,3$	40.0	25300