



17320

SUPPORTS & STOPS

Material

Steel, case-hardened and finely ground in pairs.

Technical Notes

The thickness of these parallels matches the slot width on machine tables (tolerance H8).

range H8).

Tolerances:

h_1 (height) pair tolerance $tp = IT5$.

h_1 (height) standard (single) tolerance to DIN ISO 2768m.

w_1 (width) standard (single) tolerance = h7

Other dimensions to DIN ISO 2768m.

Tips

Ideally used for stops on small and medium machines. They allow rapid alignment of the workpiece to the table.

Order No.	h_1	l_1	Pair tolerance h_1 tp	Standard tolerance h_1 DIN 7168m	w_1	w_1 tol. h7	Weight/pair g
17320.W0008	25	100	0.009	$\pm 0,2$	8	-0.015	315
17320.W0010	32	100	0.011	$\pm 0,3$	10	-0.015	500
17320.W0012	40	100	0.011	$\pm 0,3$	12	-0.018	750
17320.W0014	50	100	0.011	$\pm 0,3$	14	-0.018	1100
17320.W0016	50	160	0.011	$\pm 0,3$	16	-0.018	2000
17320.W0018	63	160	0.013	$\pm 0,3$	18	-0.018	2850
17320.W0020	63	160	0.013	$\pm 0,3$	20	-0.021	3170
17320.W0022	80	160	0.013	$\pm 0,3$	22	-0.021	4400
17320.W0024	80	160	0.013	$\pm 0,3$	24	-0.021	4800
17320.W0028	100	160	0.015	$\pm 0,3$	28	-0.021	7000

