




Studs strength class 12,9

T-Nuts & T-Bolts



21120

T-NUTS & T-BOLTS

Material

Forged steel, rolled thread, heat treated to tensile strength 12,9.

please refer to part no. 21100.

Tips

Please refer to Nos. 24000, 24300, 24400 and 25000 for appropriate T-nuts, fixture nuts, collar nuts and washers.

Technical Notes

For studs of tensile strength 8,8 and 10,9

Order No.	$d_1 \times l_1$	l_2	l_3	Weight g
21120.W0123	M12x80	15	50	55
21120.W0124	M12x100	15	63	70
21120.W0125	M12x125	15	75	90
21120.W0126	M12x160	15	100	113
21120.W0162	M16 x 80	19	50	105
21120.W0163	M16x100	19	63	130
21120.W0164	M16x125	19	75	160
21120.W0165	M16x160	19	100	218
21120.W0166	M16x200	19	125	280
21120.W0167	M16x250	19	160	325
21120.W0202	M20x125	27	70	255
21120.W0203	M20x160	27	100	330
21120.W0204	M20x200	27	125	410
21120.W0205	M20x250	27	160	510
21120.W0206	M20x315	27	200	640
21120.W0208	M20x500	27	315	1020
21120.W0243	M24x160	35	100	470
21120.W0244	M24x200	35	125	580
21120.W0245	M24x250	35	160	730
21120.W0246	M24x315	35	200	920
21120.W0247	M24x400	35	250	1160
21120.W0248	M24x500	35	315	1460