


## Threaded Insert - Solid - Inch stainless steel







22046

## Material

Inserts: stainless steel (AISI 303) or equivalent. Passivated.

Keys: stainless steel (302 CRES) or equivalent. Passivated.

## **Technical Notes**

**General tolerances:** 

 $\pm$  0,010" unless specified.

## Tap drill hole tolerances:

0,234 to 0,500 = +0,004/-0,001".

0,500 and over = +0,005/-0,001".

#### Tips

Order installation tool separately, as identified by "Inst. tool ref." in table.

## **Important Notes**

Four locking keys on external threads 7/16" and over. Two locking keys on external threads smaller than 7/16".

Installation (Inst.) drill size, countersink,

thread tap and thread depth as specified in table.

Removal drill size and drill depth as specified in table.

External inch thread allows you to machine your internal thread.

\*Unified special pitch thread.

All dimensions in inches.

Order No.	d <sub>1</sub> (mod.) tol. 2A	Thread type d <sub>1</sub>	I <sub>1</sub>	Inst. tool ref. 22050	Inst. tap drill size	Inst. c'sink dia. +0.010 - 0.000	Inst. thread tap tol. 2B	Inst. thread tap depth min.	Removal drill size	Removal drill dept
22046.W0010	5/16"-18	UNC	0.31	.W0010	0,272	0,32	5/16"-18	0,37	7/32"	1/8"
22046.W0020	3/8"-16	UNC	0,31	.W0020	0,332	0,38	3/8"-16	0,37	9/32"	1/8"
22046.W0030	7/16"-14	UNC	0,37	.W0030	0,397	0,44	7/16"-14	0,43	11/32"	3/16"
22046.W0040	1/2"-13	UNC	0,43	.W0040	0,453	0,51	1/2"-13	0,50	13/32"	3/16"
22046.W0050	9/16"-12	UNC	0,50	.W0050	0,516	0,57	9/16"-12	0,56	15/32"	3/16"
22046.W0060	5/8"-11	UNC	0,62	.W0060	0,578	0,63	5/8"-11	0,68	17/32"	3/16"
22046.W0065	11/16"-11*	UNS	0,68	.W0065	0,641	0,70	11/16"-11*	0,75	19/32"	3/16"
22046.W0070	3/4"-16	UNF	0,68	.W0070	0,703	0,76	3/4"-16	0,75	21/32"	3/16"
22046.W0075	13/16"-16	UNF	0,81	.W0075	0,766	0,82	13/16"-16	0,94	23/32"	3/16"
22046.W0080	7/8"-14	UNF	0,87	.W0080	0,828	0,88	7/8"-14	1,00	25/32"	5/16"
22046.W0090	1"-12	UNF	0,87	.W0090	0,937	1,02	1"-12	1,00	27/32"	5/16"
22046.W0100	1-1/8"-12	UNF	1,12	.W0100	1,062	1,14	1-1/8"-12	1,31	31/32"	5/16"
22046.W0110	1-1/4"-12	UNF	1,25	.W0110	1,187	1,27	1-1/4"-12	1,44	1-3/32"	5/16"
22046.W0120	1-3/8"-12	UNF	1,37	.W0120	1,312	1,39	1-3/8"-12	1,56	1-7/32"	5/16"
22046.W0130	11/16"-11*	UNS	0,68	.W0065	0,641	0,70	11/16"-11*	0,75	19/32"	5/16"
22046.W0140	13/16"-16	UNF	0,81	.W0075	0,766	0,82	13/16"-16	0,94	23/32"	5/16"



Fixing Elements



Threaded inserts are used to quickly repair stripped, damaged or worn out threads with new stronger threads, or are used in original equipment to quarantee stronger thread connections.

Wixroyd inserts are easy to install and remove, without the need for special drills, taps or pre-winder tools. The 'locking keys' on threaded inserts are easily driven down into the thread of the surrounding base material – locking the insert securely in place.








Carbon steel inserts

Stainless steel inserts

Solid inserts

## **Key Features**

- Solid, one-piece construction providing high pull-out strengths.
- Locking "keys" provide a positive mechanical lock against rotation of the insert.
- Easy installation and removal.
- Installation with standard drills and taps.
- No pre-winder tools required.
- No tangs to break off and account for in the assembly.
- For use in a wide variety of materials.
- Both metric and imperial sizes available in coarse and fine pitches.



## **Installation and Removal**

## Installation

- 1 Select desired threaded insert, and from the product data table identify the installation drill and tap sizes (note the drill is slightly oversized deliberately). Drill with standard tap drill as per product data table, and countersink with standard 82-100° countersink.
- Tap new threads with standard tap as specified in product data table.
- 3 Screw in the insert until it is 0.25 to 0.75mm (0.010 to 0.030 inch) below the surface.
- Drive locking keys down with several hammer taps on the installation tool – see product data table for correct tool.
- Insert is installed.














### Removal

Wixroyd threaded inserts, can be removed (if required) without damage to the surrounding material.







Install a replacement insert into the original tapped hole.



# **Threaded Inserts**

overview





22000 - Thinwall - Metric Use installation tool no. 22060.



22002 - Heavy Duty -Metric.

Use installation tool no. 22062.



22012 - Heavy Duty -Metric - Inch. Use installation tool

no. 22064.



22020, 22022, 22024 - Inch - Thinwall - Heavy Duty -Extra Heavy Duty. Use installation tool no. 22054-58.



**Carbon Steel** 

Solid

**Stainless Steel** 



22004 - Thinwall - Metric Use installation tool no. 22060.



22006 - Heavy Duty -Metric

Use installation tool no. 22062.



22010 - Heavy Duty -Metric - Inch. Use installation tool no. 22064.



22030 - 22034 - Inch - Thinwall - Heavy Duty -**Extra Heavy Duty** Use installation tool no. 22054, 20058.



22040 - Metric - Carbon Use installation tool no. 22052.



22042 - Metric -Stainless Steel Use installation tool no. 22052.



22044 - Inch - Carbon Use installation tool no. 22050.



22046 - Inch - Stainless Use installation tool

no. 22050.



**Installation Tools** 



22050 for 22044 & 22046



22052 for 22040 & 22042



22054, 22058 for 22020, 22024, 22030, 22034,



22060 for 22000 & 22004



ov-W22000-AP0084.1-W22064-A-TTR1760-threaded-inserts-overview-rnh- Updated - 26-10-2022



