






17440

STANDARD MANUAL CLAMPING

Material

Body: steel, case-hardened, ground and blackened.

Star grip: no. 70020 (orange).

Lever: no. 73000 (black).

Technical Notes

Suitable for simultaneous positioning and

clamping of workpieces.

The locating element is a precision element which can be assembled from either side.

Tips

The clamping and fixing part (made by the user to suit the workpiece) is screwed onto the unit.

Order No.	w ₁	w ₂ ±0.05	l ₁	d ₁ tol. H7/g5	h ₁	d ₂	d ₃	h ₂	h ₃	l ₂	l ₃	l ₄	l ₅	l ₆	l ₇	l ₈	Type	Weight g
17440.W0040	40	27	50	18	29,8	M 6	40	14,9	16,9	33	28	19	9	17	8		With palm grip	505
17440.W0050	50	33	60	22	34,8	M 8	50	17,4	19,4	42	34	24	10	21	10		With palm grip	862
17440.W0440	40	27	60	18	29,8	M 6		14,9	16,9	96	28	19	3	17	8	50	Eccentric lever	566
17440.W0450	50	33	75	22	34,8	M 8		17,4	19,4	145	34	24	4	21	10	63	Eccentric lever	1071