



18300

SUPPORTS & STOPS

Material

Bolt: steel, blackened and with a hardened head. Tensile strength 500N/mm².

and rounded head which can be used as support or setting bolt as an end stop. These bolts are normally used together with a locknut.

Technical Notes

Setting bolts are produced with a hardened

Order No.	d ₁	l ₁	l ₂	h ₁	w ₁	A/F
18300.W0031	M 3	10	2	2.0	6.4	5.5
18300.W0032	M 3	20	2	2.0	6.4	5.5
18300.W0033	M 3	30	2	2.0	6.4	5.5
18300.W0041	M 4	10	2	2.8	8.1	7.0
18300.W0042	M 4	20	2	2.8	8.1	7.0
18300.W0043	M 4	30	2	2.8	8.1	7.0
18300.W0051	M 5	20	2	3.5	9.2	8.0
18300.W0052	M 5	30	2	3.5	9.2	8.0
18300.W0053	M 5	40	2	3.5	9.2	8.0
18300.W0061	M 6	30	3	4.0	11.5	10.0
18300.W0062	M 6	40	3	4.0	11.5	10.0
18300.W0063	M 6	50	3	4.0	11.5	10.0
18300.W0081	M 8	30	4	5.5	15.0	13.0
18300.W0082	M 8	40	4	5.5	15.0	13.0
18300.W0083	M 8	50	4	5.5	15.0	13.0
18300.W0101	M10	40	5	7.0	19.6	17.0
18300.W0102	M10	50	5	7.0	19.6	17.0
18300.W0103	M10	60	5	7.0	19.6	17.0
18300.W0104	M10	70	5	7.0	19.6	17.0
18300.W0121	M12	40	5	8.0	21.9	19.0
18300.W0122	M12	50	5	8.0	21.9	19.0
18300.W0123	M12	60	5	8.0	21.9	19.0
18300.W0124	M12	70	5	8.0	21.9	19.0
18300.W0161	M16	50	6	10.0	27.7	24.0
18300.W0162	M16	60	6	10.0	27.7	24.0
18300.W0163	M16	70	6	10.0	27.7	24.0
18300.W0164	M16	80	6	10.0	27.7	24.0

