




Loose Slot Tenons for machine tool spindles

Tenons, Locating Pads & Drill



30040

TENONS, LOCATING PADS & DRILL BUSHES

Material

Steel, case-hardened (C15), blackened and ground.

Used for locating fixtures and clamping elements onto machine tables. Simply push into position after fixture or clamping element has been roughly positioned.

Technical Notes

Produced to DIN 6323.

Order No.	Type	Machine slot size w_2 tol. h6	l_1	Fixture slot size w_1 tol. h6	h_1	h_2	h_3	h_4	Weight g
30040.W0010	Type A	10	20	12	12.0	3.6	-	-	20
30040.W0012	Type A	12	32	20	14.0	5.5	-	-	50
30040.W0014	Type A	14	32	20	14.0	5.5	-	-	55
30040.W0016	Type A	16	32	20	14.0	5.5	-	-	60
30040.W0018	Type A	18	32	20	14.0	5.5	-	-	65
30040.W0011	Type B	12	20	12	28.6	-	5.5	9	45
30040.W0020	Type B	20	32	20	45.5	-	7.0	16	200
30040.W0022	Type C	22	40	20	50.5	-	7.0	18	290
30040.W0024	Type C	24	40	20	55.5	-	7.0	20	350
30040.W0028	Type C	28	40	20	61.5	-	7.0	24	460
30040.W0036	Type C	36	50	20	76.5	-	7.0	30	940