




Eccentric Levers - Male fixed

Standard Manual Clam-



18582.1

STANDARD MANUAL CLAMPING

Material

Handle: zinc die-cast, black plastic coated.
Grub screw, inner parts, adjusting nut:
steel, galvanised, or stainless steel
1.4305.

Bearing washer: Thermoplastic (POM),
glass-reinforced.

Technical Notes

Enables quick and easy clamping of work-

pieces. Withstands temperatures of up to
80° C.

Order No.	Material	w ₁	l ₁	d ₁	h ₁ max.	d ₂	d ₃	l ₂ max.	Clamping stroke s ₁	Weight g
18582.W0009	Steel	16	63	M 6	16.4	16	18.5	16	0.75	63
18582.W0012	Steel	16	63	M 6	16.4	16	18.5	30	0.75	66
18582.W0014	Steel	16	63	M 6	16.4	16	18.5	40	0.75	68
18582.W0016	Steel	16	63	M 6	16.4	16	18.5	50	0.75	68
18582.W0019	Steel	20	82	M 8	19.5	20	22.5	20	1.00	129
18582.W0020	Steel	20	82	M 8	19.5	20	22.5	25	1.00	130
18582.W0022	Steel	20	82	M 8	19.5	20	22.5	35	1.00	133
18582.W0023	Steel	20	82	M 8	19.5	20	22.5	40	1.00	135
18582.W0030	Steel	16	63	M 5	16.4	16	18.5	16	0.75	62
18582.W0031	Steel	16	63	M 5	16.4	16	18.5	20	0.75	63
18582.W0032	Steel	16	63	M 5	16.4	16	18.5	25	0.75	64
18582.W0033	Steel	16	63	M 5	16.4	16	18.5	30	0.75	65
18582.W0034	Steel	16	63	M 5	16.4	16	18.5	35	0.75	65
18582.W0035	Steel	16	63	M 5	16.4	16	18.5	40	0.75	66
18582.W0036	Steel	16	63	M 5	16.4	16	18.5	50	0.75	67
18582.W0209	Stainless	16	63	M 6	16.4	16	18.5	16	0.75	63
18582.W0212	Stainless	16	63	M 6	16.4	16	18.5	30	0.75	66
18582.W0214	Stainless	16	63	M 6	16.4	16	18.5	40	0.75	68
18582.W0216	Stainless	16	63	M 6	16.4	16	18.5	50	0.75	68
18582.W0219	Stainless	20	82	M 8	19.5	20	22.5	20	1.00	129
18582.W0220	Stainless	20	82	M 8	19.5	20	22.5	25	1.00	130
18582.W0222	Stainless	20	82	M 8	19.5	20	22.5	35	1.00	133
18582.W0223	Stainless	20	82	M 8	19.5	20	22.5	40	1.00	135
18582.W0230	Stainless	16	63	M 5	16.4	16	18.5	16	0.75	62
18582.W0231	Stainless	16	63	M 5	16.4	16	18.5	20	0.75	63
18582.W0232	Stainless	16	63	M 5	16.4	16	18.5	25	0.75	64
18582.W0233	Stainless	16	63	M 5	16.4	16	18.5	30	0.75	65
18582.W0234	Stainless	16	63	M 5	16.4	16	18.5	35	0.75	65
18582.W0235	Stainless	16	63	M 5	16.4	16	18.5	40	0.75	66
18582.W0236	Stainless	16	63	M 5	16.4	16	18.5	50	0.75	67

