



30200

TENONS, LOCATING PADS & DRILL BUSHES

Material

Cylindrical stop: steel, case-hardened and ground.
Holding plate: steel, blackened.

Screw: DIN 912, quality 8.8.

Technical Notes

Used as workpiece stops on machine

tables, and as datum points. The short form is ground to a height tolerance of $\pm 0,01\text{mm}$ and can also be used as a seating element.

Order No.	Short l_1 ± 0.01	Long l_1 ± 0.2	l_2	w_2 -0.6	d_1 ± 0.01	h_1	Screw DIN 912	T-slot w_1 tol. h6	Weight g
30200.W0110	15	-	8	10	20	6	M 6x25	10	53
30200.W0112	15	-	8	12	20	6	M 6x25	12	58
30200.W0114	25	-	9	14	32	8	M 8x35	14	202
30200.W0116	25	-	10	16	32	8	M 8x45	16	221
30200.W0118	25	-	15	18	40	10	M10x50	18	371
30200.W0122	25	-	15	20	40	14	M10x55	22	435
30200.W0128	25	-	20	22	46	16	M12x60	28	661
30200.W0210	-	25	8	10	20	6	M 6x35	10	76
30200.W0212	-	25	8	12	20	6	M 6x35	12	83
30200.W0214	-	50	9	14	32	8	M 8x60	14	357
30200.W0216	-	50	10	16	32	8	M 8x70	16	371
30200.W0218	-	50	15	18	40	10	M10x75	18	613
30200.W0222	-	50	15	20	40	14	M10x80	22	679
30200.W0228	-	50	20	22	46	16	M12x90	28	985