




Drive Blocks for machine tool spindles

Tenons, Locating Pads & Drill



30300

TENONS, LOCATING PADS & DRILL BUSHES

Material

Steel, alloyed, case-hardened, blackened and ground.

Technical Notes

Produced to DIN 2079.
Used on machine tool spindle heads for

positioning and locking of spindle head.

Order No.	Type	l_1 tol. h5	l_2 ± 0.1	w_1	d_1	d_2	h_1	h_2	For spindle head no.	Matching screw DIN 912	Weight g
30300.W0030	A	15.9	-	16.5	6.4	10.4	16.0	6.2	30	M 6x16	25
30300.W0040	A	15.9	-	19.5	6.4	10.4	16.0	6.2	40	M 6x16	31
30300.W0045	A	19.0	-	19.5	8.4	13.5	19.0	8.3	45	M 8x20	38
30300.W0050	A	25.4	-	26.5	13.0	19.0	25.0	12.3	50-55	M12x25	85
30300.W0060	A	25.4	-	45.5	13.0	19.0	25.0	12.3	60	M12x25	179
30300.W0160	B	25.4	-	45.5	13.0	19.0	25.0	12.3	60	M12x25	140
30300.W0230	C	15.9	5.5	13.5	6.4	10.4	24.5	6.2	30	M 6x25	30
30300.W0240	C	15.9	7.0	16.5	6.4	10.4	24.5	6.2	40	M 6x25	39
30300.W0245	C	19.0	7.5	17.5	8.4	13.5	26.0	10.0	45	M 8x25	47
30300.W0250	C	25.4	11.0	24.0	13.0	19.0	29.0	12.3	50	M12x30	89

