


8" Single Station Parlec Vice machinable jaws







19751

Material

Ductile iron. Powder coated paint resists flaking and peeling. 80000 psi ductile iron body with increased nickel content for improved corrosion resistance.

Technical Notes

Hardened vice base and jaw plates. Sealed

and lubricated needle roller thrust bearing for maximum life and minimum torque. Up to 12000lbs. (53379N) of clamping force. Repeatability within 0,001" (0,025mm). Outside rails of body are machined within 0,0005" (0,013mm) square to jaw. Bed height matched to size

3.310" ±0,0005" (84,07mm ±0,013mm). Footprint and distance from the keyway to stationary jaw meets industry standard.

Important Notes

All dimensions are in inches.

Order No.	Туре		Style		lb max.		h_1	I ₁	w_1	h ₂	h ₃	h ₄	h ₅	Weight Ib
19751.W0008	Single Station		Machinable Jaws				5.51	24.47	8	2.2	1.565	1.22	1.655	175
Order No.	h ₆	I ₂	l ₃	l ₄ max.	I ₅	I ₆	I ₇	I ₈	ı	9	w_2	w ₃	W_4	w ₅
19751.W0008	3.31	21.61	8.34	11	5.75	3.681	2.66	0.875	1.0)75	11.5	11	4.94	4.75

