



32440

SPRING PLUNGER & DETENT PINS

Material

Burnished, ground, hardened steel.

Technical Notes

Striker bushings are used together with spring plungers when a contact surface is required with high resistance. In particular

they are recommended for use with spring plungers equipped with high load value and those with increased spring loads.

Tips

For dimensions d2 and s, please see corresponding spring plunger. Striker bushes

are for use with Wixroyd nos. 31500, 32100, 32150, 32200 & 32300 see stated ,e' values for each type.

| Order No. | d ₁ tol. p6 | d ₂ & s | | d ₃ | l ₁ ±0.05 | Weight g |
|-------------|---------------------------|---------------------------------|--|----------------|-------------------------|-------------|
| 32440.W0004 | 4 | See corresponding plunger table | | 1.5 | 5 | 1 |
| 32440.W0006 | 6 | See corresponding plunger table | | 2.0 | 8 | 2 |
| 32440.W0008 | 8 | See corresponding plunger table | | 3.0 | 10 | 4 |
| 32440.W0010 | 10 | See corresponding plunger table | | 4.0 | 12 | 7 |
| 32440.W0012 | 12 | See corresponding plunger table | | 6.0 | 14 | 12 |
| 32440.W0016 | 16 | See corresponding plunger table | | 8.0 | 18 | 26 |

| Order No. | l ₂ | For 32100 e = | For 32150 e = | For 32200 e = | For 32300 e = |
|-------------|----------------|---------------|---------------|---------------|---------------|
| 32440.W0004 | 2 | M_4 = 0,6 | M_4 = 1,1 | M_4 = 1,1 | - |
| 32440.W0006 | 2 | M_6 = 0,6 | M_6 = 1,6 | M_6 = 2,1 | Ø 5 mm = 0,8 |
| 32440.W0008 | 2 | M_8 = 0,9 | M_8 = 1,3 | M_8 = 2,2 | Ø 6 mm = 1,1 |
| 32440.W0010 | 3 | M10 = 1,2 | M10 = 1,4 | M10 = 1,8 | Ø 8 mm = 1,2 |
| 32440.W0012 | 3 | M12 = 1,2 | M12 = 1,7 | M12 = 2,2 | Ø 10 mm = 1,9 |
| 32440.W0016 | 3 | M16 = 1,6 | M16 = 2,3 | M16 = 2,5 | Ø 12 mm = 1,9 |