




19896

VICE CLAMPING

Material

Steel (1018), case hardened, black oxide finish.

table. Fits into side groove on side of clamp - suitable for most industry standard vices.

Technical Notes

Used to secure vice to fixture of machine

Important Notes

All dimensions are in inches.

Order No.	For thread d_1	For vice size	h_1	h_2	h_3	l_1	l_2	l_3	l_4	l_5	w_1	w_2
19896.W0040	3/8	4"	0.25	0.50	0.13	1.50	0.63	0.13	0.19	0.25	1.25	0.625
19896.W0041	1/2	4"	0.25	0.50	0.13	1.50	0.63	0.13	0.19	0.25	1.25	0.625
19896.W0060	3/8	6"	0.50	0.75	0.19	2.12	0.85	0.13	0.25	0.25	1.25	0.625
19896.W0061	1/2	6"	0.50	0.75	0.19	2.12	0.85	0.13	0.25	0.25	1.25	0.625
19896.W0062	3/8	6"	0.50	0.75	0.19	2.12	0.85	0.13	0.25	0.25	1.25	0.625