

Coolant Nozzles - Press Fit

max. 10 bar

Coolant Nozzles

Material

Body: acetal. Ball: stainless steel.

Technical Notes

Max. temperature: 70°C. Max. pressure: 10 bar. symbola/symbol is an angle of adjustment either side of centre line.

Tips

d₁

Simply drill and ream hole (to H9) then press in the coolant nozzle until the body is flush.

The threaded hole in the top of the nozzle can be used for an extension tube (20020), a spray tip (20080 or 20082) or plugged with a set screw.

20044

Order No.	d ₁ tol. h9	d ₂	I_1	I ₂	α
20044.W6080	8	M 3,5x0,60	6	1.5	±35°
20044.W6100	10	M 4,0x0,70	7	2.0	±35°
20044.W6120	12	M 5,0x0,80	8	2.5	±35°
20044.W6140	14	M 6,0x1,00	10	3.0	±35°
20044.W6150	15	M 6,0x1,00	6	3.0	±35°
20044.W6160	16	M 8,0x1,25	10	3.0	±35°



12

1



COOLANT NOZZLES

Horizontal Clamping

up to 2.2 tons



Clamping Torque



11040/CL2040				
Clamping Torque	Clamping Force			
N/m	Ν			
50	23000			
40	18000			
30	12500			
25	11500			
20	9500			



11070/CL2070				
Clamping Torque	Clamping Force			
N/m	Ν			
60	16500			
50	15000			
40	12000			
30	10000			
25	8000			
20	7000			



11081/CL2081				
Clamping Torque	Clamping Force			
N/m	Ν			
5	6600			
4.5	5500			
4	4900			



10940/CL0030				
Clamping Torque	Clamping Force			
N/m	Ν			
8.5	4000			
8	3800			
7	3400			
6	3000			
5	2500			
4	2000			







Coolant Nozzles



System pressure (bar)	0.35	0.7	1.4	2.0	2.8	4.1	5.5
Orifice diameter (mm)		Flow r	ate (litres/r	ninute)			
1.02	0.32	0.45	0.64	0.77	0.91	1.18	1.41
1.57	0.86	1.14	1.68	2	2.32	2.82	3.32
2.18	1.64	2.32	3.27	3.86	4.55	5.46	6.82
2.79	2.91	4.09	6.36	7.27	8.18	10	11.37
4.06	6.36	9.09	12.73	15.91	18.18	21.82	25.46
5.59	11.37	16.82	23.64	30.46	35.46	42.28	48.19
System pressure (bar)	6.9	10.3	13.8	20.7	34.5	69.0	103.5
Orifice diameter (mm)	Flow rate (litres/minute)						
1.02	1.59	1.86	2.09	2.77	4	5.46	6.36
1.57	3.64	4.55	5.46	6.82	9.55	13.64	17.28
2.18	7.73	9.09	10.46	12.73	16.82	23.64	28.64
2.79	14.09	16.37	18.64	23.64	29.55	40.46	49.55
4.06	28.19	34.55	41.37	49.1	63.65	90.01	110.47
5.59	53.64	65.46	75.01	89.1	114.56	161.39	197.75

What Flow Rate of Coolant is Required?

Choose a nozzle with an orifice size that matches your pump's capacity.

Select an orifice size too big and coolant pressure will drop off, an orifice size too small and an inadequate amount of coolant will reach the tool tip and can result in damage.

Note: Flow rates are based on water at 20°. Actual results may vary with fluid type, extension length and aiming angle.

To calculate the average coolant exit velocity (important in some grinding operations where it is often desirable to match or exceed the peripheral velocity of the wheel) refer to the formula below. Choose an orifice size that produces sufficient back pressure to achieve the desired velocity.

Calculating Coolant Velocity

- $V = \frac{(17.11 \times 10^{-5}) \times F}{(d \times 10^{-3})^2}$
- Where;
- V = Velocity in m/s
- $C = Constant of 17.11 \times 10^{-5}$
- F = Flow rate through orifice in litres/min (see table above)
- d = Orifice diameter (mm) from product tables

Choose a nozzle extension that suits your application. Short projections are more compact and less likely to be knocked out of position by swarf or vibration. Longer extensions are easier to aim, produce a more streamline or laminar flow and shoot further.

A Word About Coolant Pumps

Nozzle Extensions

The most common coolant pump on CNC machine tools is a single stage centrifugal pump, normally designed to move high volumes of water at low pressure (typically 0.2 to 1.4 bar). Multi-stage centrifugal pumps are capable of higher pressures (typically 1.4 to 14 bar) while still producing high flow rates. Positive displacement pumps are used for very high pressure applications up to 140 bar and are generally used with small diameter orifices due to their lower flow rates.







0333 207 4497

sales@wixroyd.com