




Shoulder Nuts - Cap Head

hex drive - 303 stainless

Shoulder Screws



33664.A2

SHOULDER SCREWS

Material

Stainless steel (AISI 303, 1.4305).
Tensile strength 550 N/mm².
Proof stress min. 190 N/mm², austenitic

stainless steel.

Technical Notes

303 stainless steel provides good resi-

stance to corrosion, it is mildly magnetic.

Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2	d_3	l_2	h_1	A/F
33664.W0406-A2	4	6	M 2	6	4	3	2.0
33664.W0408-A2	4	8	M 2	6	4	3	2.0
33664.W0410-A2	4	10	M 2	6	4	3	2.0
33664.W0412-A2	4	12	M 2	6	4	3	2.0
33664.W0414-A2	4	14	M 2	6	4	3	2.0
33664.W0416-A2	4	16	M 2	6	4	3	2.0
33664.W0418-A2	4	18	M 2	6	4	3	2.0
33664.W0420-A2	4	20	M 2	6	4	3	2.0
33664.W0508-A2	5	8	M 2.5	8	5	4	2.5
33664.W0510-A2	5	10	M 2.5	8	5	4	2.5
33664.W0512-A2	5	12	M 2.5	8	5	4	2.5
33664.W0516-A2	5	16	M 2.5	8	5	4	2.5
33664.W0520-A2	5	20	M 2.5	8	5	4	2.5
33664.W0525-A2	5	25	M 2.5	8	5	4	2.5
33664.W0608-A2	6	8	M 3	10	6	5	3.0
33664.W0610-A2	6	10	M 3	10	6	5	3.0
33664.W0612-A2	6	12	M 3	10	6	5	3.0
33664.W0616-A2	6	16	M 3	10	6	5	3.0
33664.W0620-A2	6	20	M 3	10	6	5	3.0
33664.W0625-A2	6	25	M 3	10	6	5	3.0
33664.W0630-A2	6	30	M 3	10	6	5	3.0
33664.W0640-A2	6	40	M 3	10	6	5	3.0
33664.W0650-A2	6	50	M 3	10	6	5	3.0
33664.W0816-A2	8	16	M 3.5	12	11	6	4.0
33664.W0820-A2	8	20	M 3.5	12	11	6	4.0
33664.W0825-A2	8	25	M 3.5	12	11	6	4.0
33664.W0830-A2	8	30	M 3.5	12	11	6	4.0
33664.W0840-A2	8	40	M 3.5	12	11	6	4.0
33664.W0850-A2	8	50	M 3.5	12	11	6	4.0
33664.W1016-A2	10	16	M 4	14	12	7	5.0
33664.W1020-A2	10	20	M 4	14	12	7	5.0
33664.W1025-A2	10	25	M 4	14	12	7	5.0
33664.W1030-A2	10	30	M 4	14	12	7	5.0
33664.W1040-A2	10	40	M 4	14	12	7	5.0



Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2	d_3	l_2	h_1	A/F
33664.W1225-A2	12	25	M 5	20	16	8	6.0
33664.W1230-A2	12	30	M 5	20	16	8	6.0
33664.W1240-A2	12	40	M 5	20	16	8	6.0
33664.W1250-A2	12	50	M 5	20	16	8	6.0