




# Coolant Nozzles - Single Tube Ball

bendable tube - max. 33 bar

## Coolant Nozzles



20084

COOLANT NOZZLES

### Material

Ball: brass.

Tube: copper.

Max. pressure: 33 bar.


### Tips

Bendable extension tubes.

### Technical Notes

Max. temperature: 150°C.

| Order No.   | d <sub>1</sub> | d <sub>2</sub> | d <sub>3</sub> | l <sub>1</sub> |
|-------------|----------------|----------------|----------------|----------------|
| 20084.W0090 | 9              | 3.0            | 4.7            | 152.4          |
| 20084.W0100 | 10             | 3.0            | 4.7            | 152.4          |
| 20084.W0110 | 11             | 3.0            | 4.7            | 152.4          |
| 20084.W0120 | 12             | 3.0            | 4.7            | 152.4          |
| 20084.W0121 | 12             | 4.6            | 6.4            | 152.4          |
| 20084.W0140 | 14             | 3.0            | 4.7            | 152.4          |
| 20084.W0141 | 14             | 4.6            | 6.4            | 152.4          |
| 20084.W0150 | 15             | 3.0            | 4.7            | 152.4          |
| 20084.W0151 | 15             | 4.6            | 6.4            | 152.4          |
| 20084.W0180 | 18             | 3.0            | 4.7            | 152.4          |
| 20084.W0181 | 18             | 4.6            | 6.4            | 152.4          |
| 20084.W0220 | 22             | 3.0            | 4.7            | 152.4          |
| 20084.W0221 | 22             | 4.6            | 6.4            | 152.4          |
| 20084.W2370 | 3/8"           | 3.0            | 4.7            | 152.4          |
| 20084.W2500 | 1/2"           | 3.0            | 4.7            | 152.4          |
| 20084.W2501 | 1/2"           | 4.6            | 6.4            | 152.4          |
| 20084.W2630 | 5/8"           | 3.0            | 4.7            | 152.4          |
| 20084.W2631 | 5/8"           | 4.6            | 6.4            | 152.4          |






# Horizontal Clamping

up to 2.2 tons

## Clamping & Height Setting


COOLANT NOZZLES

### Clamping Torque




11040/CL2040

| Clamping Torque | Clamping Force |
|-----------------|----------------|
| N/m             | N              |
| 50              | 23000          |
| 40              | 18000          |
| 30              | 12500          |
| 25              | 11500          |
| 20              | 9500           |



11070/CL2070

| Clamping Torque | Clamping Force |
|-----------------|----------------|
| N/m             | N              |
| 60              | 16500          |
| 50              | 15000          |
| 40              | 12000          |
| 30              | 10000          |
| 25              | 8000           |
| 20              | 7000           |



11081/CL2081

| Clamping Torque | Clamping Force |
|-----------------|----------------|
| N/m             | N              |
| 5               | 6600           |
| 4.5             | 5500           |
| 4               | 4900           |



10940/CL0030

| Clamping Torque | Clamping Force |
|-----------------|----------------|
| N/m             | N              |
| 8.5             | 4000           |
| 8               | 3800           |
| 7               | 3400           |
| 6               | 3000           |
| 5               | 2500           |
| 4               | 2000           |



## What Flow Rate of Coolant is Required?

Choose a nozzle with an orifice size that matches your pump's capacity.

Select an orifice size too big and coolant pressure will drop off, an orifice size too small and an inadequate amount of coolant will reach the tool tip and can result in damage.

**Note:** Flow rates are based on water at 20°. Actual results may vary with fluid type, extension length and aiming angle.

| System pressure (bar) | 0.35                      | 0.7   | 1.4   | 2.0   | 2.8   | 4.1   | 5.5   |
|-----------------------|---------------------------|-------|-------|-------|-------|-------|-------|
| Orifice diameter (mm) | Flow rate (litres/minute) |       |       |       |       |       |       |
| 1.02                  | 0.32                      | 0.45  | 0.64  | 0.77  | 0.91  | 1.18  | 1.41  |
| 1.57                  | 0.86                      | 1.14  | 1.68  | 2     | 2.32  | 2.82  | 3.32  |
| 2.18                  | 1.64                      | 2.32  | 3.27  | 3.86  | 4.55  | 5.46  | 6.82  |
| 2.79                  | 2.91                      | 4.09  | 6.36  | 7.27  | 8.18  | 10    | 11.37 |
| 4.06                  | 6.36                      | 9.09  | 12.73 | 15.91 | 18.18 | 21.82 | 25.46 |
| 5.59                  | 11.37                     | 16.82 | 23.64 | 30.46 | 35.46 | 42.28 | 48.19 |

| System pressure (bar) | 6.9                       | 10.3  | 13.8  | 20.7  | 34.5   | 69.0   | 103.5  |
|-----------------------|---------------------------|-------|-------|-------|--------|--------|--------|
| Orifice diameter (mm) | Flow rate (litres/minute) |       |       |       |        |        |        |
| 1.02                  | 1.59                      | 1.86  | 2.09  | 2.77  | 4      | 5.46   | 6.36   |
| 1.57                  | 3.64                      | 4.55  | 5.46  | 6.82  | 9.55   | 13.64  | 17.28  |
| 2.18                  | 7.73                      | 9.09  | 10.46 | 12.73 | 16.82  | 23.64  | 28.64  |
| 2.79                  | 14.09                     | 16.37 | 18.64 | 23.64 | 29.55  | 40.46  | 49.55  |
| 4.06                  | 28.19                     | 34.55 | 41.37 | 49.1  | 63.65  | 90.01  | 110.47 |
| 5.59                  | 53.64                     | 65.46 | 75.01 | 89.1  | 114.56 | 161.39 | 197.75 |

## Calculating Coolant Velocity

To calculate the average coolant exit velocity (important in some grinding operations where it is often desirable to match or exceed the peripheral velocity of the wheel) refer to the formula below. Choose an orifice size that produces sufficient back pressure to achieve the desired velocity.

$$V = \frac{(17.11 \times 10^{-5}) \times F}{(d \times 10^{-3})^2}$$

Where;

V = Velocity in m/s

C = Constant of 17.11 x 10<sup>-5</sup>

F = Flow rate through orifice in litres/min (see table above)

d = Orifice diameter (mm) from product tables

## Nozzle Extensions

Choose a nozzle extension that suits your application. Short projections are more compact and less likely to be knocked out of position by swarf or vibration. Longer extensions are easier to aim, produce a more streamline or laminar flow and shoot further.

## A Word About Coolant Pumps

The most common coolant pump on CNC machine tools is a single stage centrifugal pump, normally designed to move high volumes of water at low pressure (typically 0.2 to 1.4 bar). Multi-stage centrifugal pumps are capable of higher pressures (typically 1.4 to 14 bar) while still producing high flow rates. Positive displacement pumps are used for very high pressure applications up to 140 bar and are generally used with small diameter orifices due to their lower flow rates.

