




Shoulder Nuts - Cap Head

hex drive - 303 stainless - blackened

Shoulder Screws



33664.B2

SHOULDER SCREWS

Material

Stainless steel (AISI 303, 1.4305), black oxide coating.
Tensile strength 550 N/mm².

Proof stress min. 190 N/mm², austenitic stainless steel.

Technical Notes

303 stainless steel provides good resistance to corrosion, it is mildly magnetic. Blackening provides some further corro-

Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2	d_3	l_2	h_1	A/F
33664.W0406-B2	4	6	M 2	6	4	3	2.0
33664.W0408-B2	4	8	M 2	6	4	3	2.0
33664.W0410-B2	4	10	M 2	6	4	3	2.0
33664.W0412-B2	4	12	M 2	6	4	3	2.0
33664.W0414-B2	4	14	M 2	6	4	3	2.0
33664.W0416-B2	4	16	M 2	6	4	3	2.0
33664.W0418-B2	4	18	M 2	6	4	3	2.0
33664.W0420-B2	4	20	M 2	6	4	3	2.0
33664.W0508-B2	5	8	M 2.5	8	5	4	2.5
33664.W0510-B2	5	10	M 2.5	8	5	4	2.5
33664.W0512-B2	5	12	M 2.5	8	5	4	2.5
33664.W0516-B2	5	16	M 2.5	8	5	4	2.5
33664.W0520-B2	5	20	M 2.5	8	5	4	2.5
33664.W0525-B2	5	25	M 2.5	8	5	4	2.5
33664.W0608-B2	6	8	M 3	10	6	5	3.0
33664.W0610-B2	6	10	M 3	10	6	5	3.0
33664.W0612-B2	6	12	M 3	10	6	5	3.0
33664.W0616-B2	6	16	M 3	10	6	5	3.0
33664.W0620-B2	6	20	M 3	10	6	5	3.0
33664.W0625-B2	6	25	M 3	10	6	5	3.0
33664.W0630-B2	6	30	M 3	10	6	5	3.0
33664.W0640-B2	6	40	M 3	10	6	5	3.0
33664.W0650-B2	6	50	M 3	10	6	5	3.0
33664.W0816-B2	8	16	M 3.5	12	11	6	4.0
33664.W0820-B2	8	20	M 3.5	12	11	6	4.0
33664.W0825-B2	8	25	M 3.5	12	11	6	4.0
33664.W0830-B2	8	30	M 3.5	12	11	6	4.0
33664.W0840-B2	8	40	M 3.5	12	11	6	4.0
33664.W0850-B2	8	50	M 3.5	12	11	6	4.0
33664.W1016-B2	10	16	M 4	14	12	7	5.0
33664.W1020-B2	10	20	M 4	14	12	7	5.0
33664.W1025-B2	10	25	M 4	14	12	7	5.0
33664.W1030-B2	10	30	M 4	14	12	7	5.0
33664.W1040-B2	10	40	M 4	14	12	7	5.0



Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2	d_3	l_2	h_1	A/F
33664.W1225-B2	12	25	M 5	20	16	8	6.0
33664.W1230-B2	12	30	M 5	20	16	8	6.0
33664.W1240-B2	12	40	M 5	20	16	8	6.0
33664.W1250-B2	12	50	M 5	20	16	8	6.0