




Shoulder Nuts - Cap Head

hex drive - 316 stainless - blackened

Shoulder Screws



33664.B4

SHOULDER SCREWS

Material

Stainless steel (AISI 316, 1.440), black oxide coating.
Tensile strength 480 N/mm².

Proof stress min. 200 N/mm², austenitic stainless steel.

Technical Notes

It is non-magnetic.
Blackening provides some further corrosion resistance.

Order No.	d ₁ +0.000 -0.025	l ₁ +0.05 -0.00	d ₂	d ₃	l ₂	h ₁	A/F
33664.W0406-B4	4	6	M 2	6	4	3	2.0
33664.W0408-B4	4	8	M 2	6	4	3	2.0
33664.W0410-B4	4	10	M 2	6	4	3	2.0
33664.W0412-B4	4	12	M 2	6	4	3	2.0
33664.W0414-B4	4	14	M 2	6	4	3	2.0
33664.W0416-B4	4	16	M 2	6	4	3	2.0
33664.W0418-B4	4	18	M 2	6	4	3	2.0
33664.W0420-B4	4	20	M 2	6	4	3	2.0
33664.W0508-B4	5	8	M 2.5	8	5	4	2.5
33664.W0510-B4	5	10	M 2.5	8	5	4	2.5
33664.W0512-B4	5	12	M 2.5	8	5	4	2.5
33664.W0516-B4	5	16	M 2.5	8	5	4	2.5
33664.W0520-B4	5	20	M 2.5	8	5	4	2.5
33664.W0525-B4	5	25	M 2.5	8	5	4	2.5
33664.W0608-B4	6	8	M 3	10	6	5	3.0
33664.W0610-B4	6	10	M 3	10	6	5	3.0
33664.W0612-B4	6	12	M 3	10	6	5	3.0
33664.W0616-B4	6	16	M 3	10	6	5	3.0
33664.W0620-B4	6	20	M 3	10	6	5	3.0
33664.W0625-B4	6	25	M 3	10	6	5	3.0
33664.W0630-B4	6	30	M 3	10	6	5	3.0
33664.W0640-B4	6	40	M 3	10	6	5	3.0
33664.W0650-B4	6	50	M 3	10	6	5	3.0
33664.W0816-B4	8	16	M 3.5	12	11	6	4.0
33664.W0820-B4	8	20	M 3.5	12	11	6	4.0
33664.W0825-B4	8	25	M 3.5	12	11	6	4.0
33664.W0830-B4	8	30	M 3.5	12	11	6	4.0
33664.W0840-B4	8	40	M 3.5	12	11	6	4.0
33664.W0850-B4	8	50	M 3.5	12	11	6	4.0
33664.W1016-B4	10	16	M 4	14	12	7	5.0
33664.W1020-B4	10	20	M 4	14	12	7	5.0
33664.W1025-B4	10	25	M 4	14	12	7	5.0
33664.W1030-B4	10	30	M 4	14	12	7	5.0
33664.W1040-B4	10	40	M 4	14	12	7	5.0



Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2	d_3	l_2	h_1	A/F
33664.W1225-B4	12	25	M 5	20	16	8	6.0
33664.W1230-B4	12	30	M 5	20	16	8	6.0
33664.W1240-B4	12	40	M 5	20	16	8	6.0
33664.W1250-B4	12	50	M 5	20	16	8	6.0