




One-Touch Fastener- Cam Locking - quarter turn - t-handle grip - steel



One Touch
Fasteners



33947

ONE TOUCH FASTENERS

Material

Body: steel, nickel plated.
Shank: steel, nickel plated.
Pin: stainless steel, SUS304.
Knob: stainless steel, SUS304.
Spring: stainless steel.

Technical Notes

One-touch fasteners are the ideal solution for applications requiring rapid and recurring change over of tooling or set ups. Use in applications as diverse as bottling processes, machine covers, changing of cogs and drive belts. One-touch fasteners

provide a quick, simple and secure change over solution - no time waste in unfasting screws or other permanent fixings, and no opportunity for lost fixings in your machinery.
Temperature resistant to 200°C.

Important Notes

One-touch fastener offers full retraction of clamping shank when part is unlocked, this offer's the benefit of enabling panels to be slid into position - especially useful with larger or oversized panels, and enables its use on sliding or linear rail applications to provide positive location

and clamping of parts.





Actuation:

- Turn handle to off position, and ensure the shank is fully retracted.
- Place or slide the over in place and position over the locating bush.
- Turn handle to on position for clamping, an audible click is heard when fully clamped.
- To release, turn handle back to off position, the shank is fully retracted into clamp body assisted by the return spring.

Order No.	Single panel thickness	Clamping force N	d ₁	d ₂	d ₃	d ₄	d ₅	d ₆	l ₁	l ₂	h ₁	h ₂	h ₃	Shear strength N	Tensile strength N	Weight g
33947.W1005	6-10	60	5	14	25	25	21	M2x0,4	15,5	5,5	30	20,0	6,5	1800	1200	40
33947.W1408	6-14	90	8	18	34	34	28	M3x0,5	17,0	5,5	38	26,5	10,0	3200	400	100



One-Touch Fasteners - Alternatives to Screws





Easy & Secure! For Quick Changeover with No Tools!








One-Touch Change Over



Installation and Removal of Rotary Blades and Changes of Shooters



Changes of Star Wheels and Guide Plates




Changes of Pusher and Changes of Chuck Handling Machines




Operating Principle

- ① The shank retracts at the unclamping position to enable operations without interference with the base panel.
- ② When the pin contacts along the cam surface in the cam receptacle, the spring gets compressed to press down the panel.



Operating Instructions


- ① Ensure that the knob is positioned at the "OFF" mark and the pin is retracted.
- ② Locate the cam receptacle directly under the fastener. Insert retracted pin by pressing the knob down.
- ③ Turn the knob to the "ON" mark for clamping. The knob clicks when clamped. Turning the knob to the "OFF" position, the pin returns automatically to the unclamping position.






Applications

Changes of Fixture Plates



Lock for Doors



Adjustment of Workpiece Guides

