




Construction Balls

imperial and metric - shoulder type

Gauging & Inspection



20512

GAUGING & INSPECTION

Material

Hardened and ground steel (8620 steel).

Technical Notes

Concentricity of ball to shank: ,0002 T.I.R.

Important Notes

Used as reference points for inspection applications in conjunction with CMMs to accurately measure the work piece.

Order No.	Type	d ₁ inch ±0.0002 in ±0.005 mm	d ₂ +0.0000 in -0.0004 in. +0.000 mm -0.010 mm	d ₃	d ₄ UNC-2B	l ₁	l ₂ ±0.0002 in ±0.005 mm	Weight g
20512.W0006	Inch	0,500	0,250	1/2"	6-32x3/16"	5/8"	0,313	13,6
20512.W0010	Inch	0,500	0,250	1/2"		5/8"	0,313	13,6
20512.W0012	Metric	6	3	6		16	6	4,5
20512.W0050	Metric	10	5	10		20	10	13,6
20512.W0051	Metric	12	6	12		22	12	13,6