
Thrust Screws - Ball Ended headless - short -flat faced ball





34060

Material

Body: steel, heat-treated, 1200 \pm 100 N/ mm².

Ball: ball bearing steel, hardened.

Technical Notes

These short ball ended thrust screws are

particularly suited for use with parallel shanks DIN 1835E, in combination with either Whistle Notch or Weldon Tool Holding fixtures. Maximised load transmission due to movable ball.

Order No.	Ball type	d_1	d_2	d ₃	I_1	A/F	Static load kN	Weight g
							max.	
34060.W0641	Flat, Plain	M14	7.2	8.5	16	6	30	13
34060.W0660	Flat, Plain	M16	7.2	8.5	16	8	30	16
34060.W0682	Flat, Plain	M18x2	10.7	12.0	20	10	60	25
34060.W0692	Flat, Plain	M20x2	10.7	12.0	20	10	60	32
34060.W0693	Flat, Plain	M20x2	10.7	12.0	25	10	60	42
34060.W0730	Flat. Plain	M24x2	13.5	15.0	25	12	90	59





Positioning Elements

Wixroyd Self-Aligning Pads & Thrust Screws



Clamping, supporting and aligning non-parallel and uneven surfaces is greatly simplified with the use of Wixroyd self-aligning pads and thrust screws. Available with ridged faces for improved holding of cast components, or plastic faces for holding more delicate parts.




Self-aligning Thrust Screws

34000 to 34060 - Self-aligning thrust screws in sizes M6 to M24, ideal for clamping or supporting non-parallel surfaces.










Self-aligning Pads

34080 to 34121 - Self-aligning pads, both male and female mounting, ideal for accommodating variations between parts in fixtures.









Thrust Screws

34140 to 34160 - Thrust screws, with either brass or thermoplastic pads, are suitable for gentle clamping and positioning more delicate parts.





