




Levelling Feet - Heavy Duty

bolt down option, bolt steel

Levelling Feet



34726

LEVELLING FEET

Material

Pad: polyamide reinforced by fibre glass with anti-slip pad.
Bolt: steel (C40)

Technical Notes

Load values refer to static loads, located at half the screw height.
When vibrations or dynamic loads are

present these values should be reduced.

Order No.	d ₁	d ₂	d ₃	d ₄	l	h ₁	h ₂	h ₃	A/F	Load kN max.
34726.W1600	M16	123	12.5	73	50	110	60	40	20	35
34726.W1601	M16	123	12.5	73	75	135	60	40@	20	35
34726.W1602	M16	123	12.5	73	100	160	60	40@	20	35
34726.W1603	M16	123	12.5	73	125	185	60	40@	20	35
34726.W1604	M16	123	12.5	73	150	210	60	40	20	35
34726.W1605	M16	123	12.5	73	175	235	60	40	20	35
34726.W1606	M16	123	12.5	73	200	260	60	40	20	35
34726.W1607	M16	123	12.5	73	225	288	60	40	20	35
34726.W2000	M20	123	12.5	73	75	135	60	40	20	35
34726.W2001	M20	123	12.5	73	100	160	60	40	20	35
34726.W2002	M20	123	12.5	73	125	185	60	40	20	35
34726.W2003	M20	123	12.5	73	150	210	60	40	20	35
34726.W2004	M20	123	12.5	73	175	235	60	40	20	35
34726.W2005	M20	123	12.5	73	200	260	60	40	20	35
34726.W2006	M20	123	12.5	73	225	285	60	40	20	35
34726.W2007	M20	123	12.5	73	250	310	60	40	20	35
34726.W2400	M24	123	12.5	73	75	135	60	40	20	35
34726.W2401	M24	123	12.5	73	100	160	60	40	20	35
34726.W2402	M24	123	12.5	73	125	185	60	40	20	35
34726.W2403	M24	123	12.5	73	150	210	60	40	20	35
34726.W2404	M24	123	12.5	73	175	235	60	40	20	35
34726.W2405	M24	123	12.5	73	200	260	60	40	20	35
34726.W2406	M24	123	12.5	73	225	285	60	40	20	35
34726.W2407	M24	123	12.5	73	250	310	60	40	20	35
34726.W3000	M30	123	12.5	73	100	161	60	40	20	35
34726.W3001	M30	123	12.5	73	125	186	60	40	20	35
34726.W3002	M30	123	12.5	73	150	211	60	40	20	35
34726.W3003	M30	123	12.5	73	175	236	60	40	20	35
34726.W3004	M30	123	12.5	73	200	261	60	40	20	35
34726.W3005	M30	123	12.5	73	225	286	60	40	20	35
34726.W3006	M30	123	12.5	73	250	311	60	40	20	35