




Levelling Feet

bolt down option, bolt **stainless steel**



Levelling Feet



34744

LEVELLING FEET

Material

Pad: polyamide reinforced by fibre glass with anti-slip pad.
Bolt: stainless steel AISI 304.

Technical Notes

Load values refer to static loads, located at half the screw height.
When vibrations or dynamic loads are

present these values should be reduced.
Larger pad size allows for bolt down holes to be drilled through.



Order No.	d ₁	l ₁	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	A/F	Load kN max.
34744.W1000	M10	50	83	8.5	55	91	38	27	14	15
34744.W1001	M10	75	83	8.5	55	116	38	27	14	15
34744.W1002	M10	100	83	8.5	55	141	38	27	14	15
34744.W1003	M10	125	83	8.5	55	166	38	27	14	15
34744.W1200	M12	50	83	8.5	55	91	38	27	14	15
34744.W1201	M12	75	83	8.5	55	116	38	27	14	15
34744.W1202	M12	100	83	8.5	55	141	38	27	14	15
34744.W1203	M12	125	83	8.5	55	166	38	27	14	15
34744.W1400	M14	50	83	8.5	55	91	38	27	14	20
34744.W1401	M14	75	83	8.5	55	116	38	27	14	20
34744.W1402	M14	100	83	8.5	55	141	38	27	14	20
34744.W1403	M14	125	83	8.5	55	166	38	27	14	20
34744.W1404	M14	150	83	8.5	55	191	38	27	14	20
34744.W1405	M14	175	83	8.5	55	216	38	27	14	20
34744.W1600	M16	50	83	8.5	55	94	41	27	13	20
34744.W1601	M16	75	83	8.5	55	119	41	27	13	20
34744.W1602	M16	100	83	8.5	55	144	41	27	13	20
34744.W1603	M16	125	83	8.5	55	169	41	27	13	20
34744.W1604	M16	150	83	8.5	55	194	41	27	13	20
34744.W1605	M16	175	83	8.5	55	219	41	27	13	20
34744.W1606	M16	200	83	8.5	55	244	41	27	13	20
34744.W1607	M16	50	103	12.5	73	104	51	32	20	25
34744.W1608	M16	75	103	12.5	73	129	51	32	20	25
34744.W1609	M16	100	103	12.5	73	154	51	32	20	25
34744.W1610	M16	125	103	12.5	73	179	51	32	20	25
34744.W1611	M16	150	103	12.5	73	204	51	32	20	25
34744.W1612	M16	175	103	12.5	73	229	51	32	20	25
34744.W1613	M16	200	103	12.5	73	254	51	32	20	25
34744.W1614	M16	225	103	12.5	73	279	51	32	20	25
34744.W2000	M20	75	83	8.5	55	119	41	27	17	20
34744.W2001	M20	100	83	8.5	55	144	41	27	17	20
34744.W2002	M20	125	83	8.5	55	169	41	27	17	20
34744.W2003	M20	150	83	8.5	55	194	41	27	17	20



Order No.	d ₁	l ₁	d ₂	d ₃	d ₄	h ₁	h ₂	h ₃	A/F	Load kN max.
34744.W2004	M20	175	83	8.5	55	219	41	27	17	20
34744.W2005	M20	200	83	8.5	55	244	41	27	17	20
34744.W2006	M20	225	83	8.5	55	269	41	27	17	20
34744.W2007	M20	75	103	12.5	73	129	51	32	20	25
34744.W2008	M20	100	103	12.5	73	154	51	32	20	25
34744.W2009	M20	125	103	12.5	73	179	51	32	20	25
34744.W2010	M20	150	103	12.5	73	204	51	32	20	25
34744.W2011	M20	175	103	12.5	73	229	51	32	20	25
34744.W2012	M20	200	103	12.5	73	254	51	32	20	25
34744.W2013	M20	225	103	12.5	73	279	51	32	20	25
34744.W2014	M20	250	103	12.5	73	304	51	32	20	25
34744.W2400	M24	75	103	12.5	73	129	51	32	20	25
34744.W2401	M24	100	103	12.5	73	154	51	32	20	25
34744.W2402	M24	125	103	12.5	73	179	51	32	20	25
34744.W2403	M24	150	103	12.5	73	204	51	32	20	25
34744.W2404	M24	175	103	12.5	73	229	51	32	20	25
34744.W2405	M24	200	103	12.5	73	280	51	32	20	25
34744.W2406	M24	250	103	12.5	73	302	51	32	20	25
34744.W2407	M24	250	103	12.5	73	305	51	32	20	25



All levelling feet can be produced with the following fixing types:



Thread versions

- Metric thread - coarse pitch (standard)
- Metric thread - fine pitch
- Thread gas 55°
- Imperial thread Unc
- Whitworth thread

* For non-standard threads a minimum order will apply.

Levelling Feet from Automation Components

LEVELLING FEET