



Fixed Slot Tenons with cylindrical fastening

Tenons, Locating Pads & Drill



30060

TENONS, LOCATING PADS & DRILL BUSHES

Material

Steel, case-hardened (C15), blackened and ground.

Technical Notes

Fixed type tenons, used in pairs, are

screwed onto the bases of vices and fixtures having standard slot sizes of 20mm. The tenon interfaces into machine T-slots of varying widths. For heavy fixtures use loose tenons no. 30040.

Order No.	Machine slot Size w_1 tol. h6	l_1	Fixture slot size w_2 tol. h6	h_1	h_2	For screws DIN 84 & DIN 912	Weight g
30060.W0010	10	22	20	10	5.5	M 6x10	20
30060.W0012	12	22	20	10	5.5	M 6x10	25
30060.W0014	14	25	20	10	5.5	M 6x16	28
30060.W0016	16	25	20	10	5.5	M 6x16	30
30060.W0018	18	25	20	10	5.5	M 6x16	30
30060.W0022	22	32	20	12	5.5	M 6x16	50
30060.W0024	24	32	20	12	5.5	M 6x16	55
30060.W0028	28	32	20	12	5.5	M 6x16	60
30060.W0036	36	32	20	12	5.5	M 6x16	75