


# Index Plungers - Pull Grip

non-locking - ALL stainless



# 32702



lock nut  
32700.W0515 - .W0520



### Material

**All Stainless Steel Type-**  
Body: stainless steel 1.4305 (AISI 303).  
Pin: stainless steel 1.4305 (AISI 303), nickel plated.  
Grip: stainless steel 1.4305 (AISI 303).  
Spring: stainless steel 1.4310 (AISI 301).

### Technical Notes

**"Non Locking" type-** pin simply springs back when pull ring released. Thread recess on body allows full engagement of thread length. Hexagon collar improves leverage for secure installation. Temperature resistance from -30° to +80°C. Distance collars no. 32750 can be used to adapt screw length.

### Tips

Complete stainless steel construction designed with specific demands of food processing, pharmaceutical and water treatment industries in mind. Grip non-removable. Spring Loads\* = statistical average.

| Order No.   | Type        | d <sub>1</sub><br>-0,02<br>-0,04 | d <sub>2</sub> | d <sub>3</sub> | l <sub>1</sub><br>≈ | l <sub>2</sub><br>min. | l <sub>3</sub> | l <sub>4</sub> | l <sub>6</sub><br>min. | a/f | Spring<br>load*<br>f <sub>1</sub><br>N | Spring<br>load*<br>f <sub>2</sub><br>N | ±g<br>g |
|-------------|-------------|----------------------------------|----------------|----------------|---------------------|------------------------|----------------|----------------|------------------------|-----|--|--|---------|
| 32702.W0705 | Non locking | 5                                | M10x1,0        | 21             | 45,0                | 5                      | 17             | 5              | 15                     | 12  | 6,0                                    | 14                                     | 39,0    |
| 32702.W0706 | Non locking | 6                                | M12x1,5        | 25             | 54,5                | 6                      | 20             | 6              | 17                     | 14  | 5,5                                    | 13                                     | 65,0    |
| 32702.W0707 | Non locking | 8                                | M16x1,5        | 31             | 69,0                | 8                      | 26             | 8              | 23                     | 19  | 11,5                                   | 28                                     | 132,0   |
| 32702.W0710 | Non locking | 10                               | M20x1,5        | 31             | 80,0                | 10                     | 33             | 10             | 30                     | 22  | 23,0                                   | 54                                     | 175,0   |
| 32700.W0515 | Lock Nut    | -                                | M10x1,0        | -              | -                   | -                      | -              | -              | -                      | -   | -                                      | -                                      | 5,2     |
| 32700.W0516 | Lock Nut    | -                                | M12x1,5        | -              | -                   | -                      | -              | -              | -                      | -   | -                                      | -                                      | 7,4     |
| 32700.W0518 | Lock Nut    | -                                | M16x1,5        | -              | -                   | -                      | -              | -              | -                      | -   | -                                      | -                                      | 18,0    |
| 32700.W0520 | Lock Nut    | -                                | M20x1,5        | -              | -                   | -                      | -              | -              | -                      | -   | -                                      | -                                      | 32,0    |






## A wide selection of solutions

- Locating and positioning.
- Indexing.
- Securing.
- Positive locking.
- Rapid adjustment of all kinds of tables, platforms and fixtures.
- Machine and fixture design.
- OEM products.
- Sports equipment.
- Medical aides (wheelchairs etc.).
- Aerospace.
- Machine cabinets.


## Applications



Steel with plastic grip



Stainless with plastic grip



Stainless body and grip


## Materials



Locking (park)



Non locking (spring back)



Push pull

## Locking or non locking



Standard grip



Lever grip



T-handle



Pull ring



Threaded for bespoke handle

## Handling and actuation methods



Fine threaded (standard)



Coarse thread



Flange mount



Thin wall mount



Weldable

## Mounting options


- Unless otherwise stated, grips on index plungers are not removeable.
- Many of the pins on index plungers are toleranced to either the pin or the hole. Please refer to the specific product table.
- Index plungers are not recommended for shear load applications.

### Pin Tol. Hole Tol.

|   |                |                |
|---|----------------|----------------|
| ① | $h_9$          | +0,03<br>+0,08 |
| ② | -0,02<br>-0,04 | H <sub>7</sub> |

## Additional technical notes

- s** Stroke, or movement of plunger's pin.
- f<sub>1</sub>** The force required in Newtons (N) to overcome the static strength of the spring and achieve initial movement of the plunger's pin.
- f<sub>2</sub>** The force required in Newtons (N) to fully compress the spring until the pin is fully depressed against the plunger's body.



## Spring loads

# Computing the strength of index plungers


for shear loads / flexure loads of the plunger pin



## Flexure loads

As soon as a gap  $l$  exists between the mounting plate in which the index plunger is installed, and the mating or base plate, the load must be considered to be as per a flexure load, with rod clamped at one side.

With this approach, the calculation is made against the bending of the index plunger.



## Formulas for computation

### Resistance torque

$$W = \frac{\pi \times d^3}{32}$$

### Flexural stress

$$M_b = \sigma_b \times W$$

### Flexural strength

$$F = \frac{M_b}{l} = \frac{\sigma_b \times \pi \times d^3}{l \times 32}$$

## Material characteristics

The yield or substitute yield limit ( $R_e / R_p 0,2$ ) shown in the table opposite has been determined in tension tests involving tension specimen in accordance with DIN 50125-B6-30.

These tests constitute the basis for the load bearing details given.

| Material Description | Material no. | $R_e$<br>in N/mm <sup>2</sup> (≈ per. flexural tension $\sigma_b$ ) |
|----------------------|--------------|---|
| C45Pb                | 1.0504       | 560   |
| X 10 CrNiS 18 9A     | ISI 303      | 580   |

## Calculation example, load values

Example:

Index plungers with a bolt diameter of 5 mm made of steel with a yield limit of  $R_e = 560 \text{ N/mm}^2$ , calculation against permanent deformation, the maximum permissible flexural strength is calculated as:

$$F_{\text{per}} = \frac{560 \text{ N/mm}^2 \times \pi \times (5\text{mm})^3}{2\text{mm} \times 32} = 3430 \text{ N}$$

| d<br>Bolt diameter | max. flexural strength $F$ in N,<br>acc. to material and gap $l$ differentiated |          |                                    |          |
|--------------------|---|----------|------------------------------------|----------|
|                    | C45Pb/1.0504<br>l = 2 mm  | l = 3 mm | X 10 CrNiS 18 9/1.4305<br>l = 2 mm | l = 3 mm |
| 3                  | 740   | 490      | 760                                | 510      |
| 4                  | 1750  | 1170     | 1820                               | 1210     |
| 5                  | 3430  | 2290     | 3550                               | 2370     |
| 6.5                | 930   | 3950     | 6140                               | 4100     |
| 8                  | 14070   | 9380     | 14570                              | 9710     |
| 10                 | 27480   | 18320    | 28470                              | 18980    |
| 12                 | 47490   | 31660    | 49190                              | 32790    |
| 16                 | 90070   | 102940   | 93290                              | 119020   |

## Safety information

On principle, the design also needs an adequate safety coefficient to be taken into account. The usual safety coefficients under static load 1.2 to 1.5; pulsating 1.8 to 2.4 and alternating 3 to 4.

Disclaimer:

You should carry out your own test series to verify whether a certain product is suitable for your specific applications.

# Computing the strength of index plungers

for shear loads / flexure loads of the plunger pin



## Shear loads


Providing only a very small gap exists between the mounting plate in which the index plunger is installed, and the mounting plate or base plate, the load can be calculated as a clean shear action.

As this is normally not the case, the "flexure" load should be used - see following page.

Approximately 80 % of the bolt's tensile strength is assumed for the shear strength. This approach calculates against the tensile strength  $R_m$ , i.e. against the index pin shearing off.

To ensure the permanent and proper function of the index plunger, the yield limit  $R_e$  must be considered in place of the tensile strength  $R_m$ .

Stop using the index plunger if the pin is damaged or deformed.



## Formulas for computation

### Bolt cross-section

$$S = \frac{d^2 \times \pi}{4}$$

### Limit tension

$$\tau_a = 0,8 \times R_m$$

### Shear force

$$F = S \times \tau_a = \frac{d^2 \times \pi}{4} \times 0,8 \times R_m$$

## Material characteristics

The tensile strength shown in the table opposite ( $R_m$ ) and the yield or substitute yield limit ( $R_e / R_p 0,2$ ) have been determine in tension tests involving tension specimen in accordance with DIN 50125- B6-30

These tests constitute the basis for the load bearing details given.

| Material Description | Material no. | $R_e$ in N/mm <sup>2</sup> | $R_m$ in N/mm <sup>2</sup> |
|----------------------|--------------|----------------------------|----------------------------|
| C45Pb                | 1.0504       | 560                        | 640                        |
| X 10 CrNiS 18 9A     | ISI 303      | 580                        | 740                        |

## Calculation example, load values

Example:

Index plungers with a bolt diameter of 6 mm made of Stainless Steel with a yield limit of  $R_e = 580 \text{ N/mm}^2$ , calculation against permanent deformation, the maximum permissible shear stress is calculated as:

$$F_{per} = \frac{(6 \text{ mm})^2 \times \pi}{4} \times 0,8 \times 580 \text{ N/mm}^2 = 13120 \text{ N}$$

| d<br>Bolt diameter | max. force F in N,<br>acc. to material and strength value differs |          |                        |          |
|--------------------|---|----------|------------------------|----------|
|                    | C45Pb/1.05045   |          | X 10 CrNiS 18 9/1.4305 |          |
|                    | at $R_e$  | at $R_m$ | at $R_e$               | at $R_m$ |
| 3                  | 3160  | 3610     | 3270                   | 4180     |
| 4                  | 5620  | 6430     | 5830                   | 7430     |
| 5                  | 790   | 10050    | 9110                   | 11620    |
| 6                  | 12660   | 14470    | 13120                  | 16730    |
| 8                  | 22510   | 25730    | 23320                  | 29750    |
| 10                 | 35180   | 40210    | 36440                  | 46490    |
| 12                 | 50660   | 57900    | 52470                  | 66950    |
| 16                 | 90070   | 102940   | 93290                  | 119020   |

## Safety information

On principle, the design also needs an adequate safety coefficient to be taken into account. The usual safety coefficients under static load 1.2 to 1,5; pulsating 1.8 to 2.4 and alternating 3 to 4.

Disclaimer:

You should carry out your own test series to verify whether a certain product is suitable for your specific applications.