




Captive Screws - Countersunk

hex drive - 316 stainless, blackened

Captive Screws



36684.B4

MADE IN BRITAIN

CAPTIVE SCREWS

Material

Stainless steel (AISI 316, 1.440), black oxide coating. Tensile strength 480 N/mm². Proof stress min. 200 N/mm², austenitic stainless steel.

Also available on request in steel (anodised, black oxide or zinc plated), brass, aluminium etc.

Technical Notes

Used to comply with the Machinery Direc-

tive 2006/42/EC. Often used with our captive washers (36691) or retaining flanges (36692 - for sheet metal applications). The use of our captive washers should be considered when fitted in panels with unthreaded holes.

Important Notes

Please note that these screws have a reduced diameter shank and should not be tightened to the recommended torque for

an equivalent machine screw of size d₁. To accommodate the slight undercut at the top of the shank, the hex socket is smaller than on a similar threaded machine screw.

Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	l ₂ ±0.25	d ₃ max.	d ₄ min.	h ₁ max.	A/F
36684.W0210-B4	M 2	10	1.2	3.5	3.8	2.5	1.20	1.0
36684.W0212-B4	M 2	12	1.2	3.5	3.8	2.5	1.20	1.0
36684.W0216-B4	M 2	16	1.2	3.5	3.8	2.5	1.20	1.0
36684.W0220-B4	M 2	20	1.2	3.5	3.8	2.5	1.20	1.0
36684.W0251-B4	M 2.5	10	1.7	3.7	4.7	2.8	1.80	1.3
36684.W0252-B4	M 2.5	12	1.7	3.7	4.7	2.8	1.80	1.3
36684.W0253-B4	M 2.5	16	1.7	3.7	4.7	2.8	1.80	1.3
36684.W0254-B4	M 2.5	20	1.7	3.7	4.7	2.8	1.80	1.3
36684.W0308-B4	M 3	8	2.0	4.5	5.6	3.5	1.65	1.5
36684.W0310-B4	M 3	10	2.0	4.5	5.6	3.5	1.65	1.5
36684.W0312-B4	M 3	12	2.0	4.5	5.6	3.5	1.65	1.5
36684.W0316-B4	M 3	16	2.0	4.5	5.6	3.5	1.65	1.5
36684.W0320-B4	M 3	20	2.0	4.5	5.6	3.5	1.65	1.5
36684.W0325-B4	M 3	25	2.0	4.5	5.6	3.5	1.65	1.5
36684.W0330-B4	M 3	30	2.0	4.5	5.6	3.5	1.65	1.5
36684.W0335-B4	M 3	35	2.0	4.5	5.6	3.5	1.65	1.5
36684.W0340-B4	M 3	40	2.0	4.5	5.6	3.5	1.65	1.5
36684.W0410-B4	M 4	10	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0412-B4	M 4	12	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0414-B4	M 4	14	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0416-B4	M 4	16	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0420-B4	M 4	20	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0425-B4	M 4	25	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0430-B4	M 4	30	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0435-B4	M 4	35	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0440-B4	M 4	40	2.8	6.0	7.5	4.5	2.20	2.0



Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	l ₂ ±0.25	d ₃ max.	d ₄ min.	h ₁ max.	A/F
36684.W0450-B4	M 4	50	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0460-B4	M 4	60	2.8	6.0	7.5	4.5	2.20	2.0
36684.W0512-B4	M 5	12	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0514-B4	M 5	14	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0516-B4	M 5	16	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0520-B4	M 5	20	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0525-B4	M 5	25	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0530-B4	M 5	30	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0535-B4	M 5	35	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0540-B4	M 5	40	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0550-B4	M 5	50	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0560-B4	M 5	60	3.7	7.5	9.2	5.5	2.50	2.5
36684.W0616-B4	M 6	16	4.2	8.0	11.0	6.5	3.00	3.0
36684.W0620-B4	M 6	20	4.2	8.0	11.0	6.5	3.00	3.0
36684.W0625-B4	M 6	25	4.2	8.0	11.0	6.5	3.00	3.0
36684.W0630-B4	M 6	30	4.2	8.0	11.0	6.5	3.00	3.0
36684.W0635-B4	M 6	35	4.2	8.0	11.0	6.5	3.00	3.0
36684.W0640-B4	M 6	40	4.2	8.0	11.0	6.5	3.00	3.0
36684.W0650-B4	M 6	50	4.2	8.0	11.0	6.5	3.00	3.0
36684.W0660-B4	M 6	60	4.2	8.0	11.0	6.5	3.00	3.0
36684.W0820-B4	M 8	20	6.0	10.0	15.0	8.5	4.10	4.0
36684.W0825-B4	M 8	25	6.0	10.0	15.0	8.5	4.10	4.0
36684.W0830-B4	M 8	30	6.0	10.0	15.0	8.5	4.10	4.0
36684.W0840-B4	M 8	40	6.0	10.0	15.0	8.5	4.10	4.0
36684.W0850-B4	M 8	50	6.0	10.0	15.0	8.5	4.10	4.0
36684.W0860-B4	M 8	60	6.0	10.0	15.0	8.5	4.10	4.0