




Captive Screws - Cheese Head slot drive - 316 stainless, blackened

Captive Screws




36694.B4

CAPTIVE SCREWS



application examples :-
counterbore length 'x₁' should be > l₂



Material

Stainless steel (AISI 316, 1.440), black oxide coating. Tensile strength 480 N/mm². Proof stress min. 200 N/mm², austenitic stainless steel.

Also available on request in steel (anodised, black oxide or zinc plated) stainless steel (AISI 303, 1.4305), brass, aluminium etc.

Technical Notes

Used to comply with the Machinery Direc-

tive 2006/42/EC. Generally to ISO 1207. Often used with our captive washers (36691) or retaining flanges (36692 - for sheet metal applications). The use of our captive washers should be considered when fitted in panels with unthreaded holes.

Tips

Other head drive styles - add suffix:

-TX for Torx (hexalobular).

-PZ for Pozidrive.

-SE for snake-eye security.

Important Notes

Please note that these screws have a reduced diameter shank and should not be tightened to the recommended torque for an equivalent machine screw of size d₁.

Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	l ₂ ±0.25	d ₃	d ₄ min.	h ₁	h ₂	w ₁
36694.W2010-B4	M 2	10	1.2	3.0	3.8	2.5	1.3	0.85	0.5
36694.W2012-B4	M 2	12	1.2	3.0	3.8	2.5	1.3	0.85	0.5
36694.W2016-B4	M 2	16	1.2	3.0	3.8	2.5	1.3	0.85	0.5
36694.W2020-B4	M 2	20	1.2	3.0	3.8	2.5	1.3	0.85	0.5
36694.W2510-B4	M 2.5	10	1.7	3.7	4.5	2.8	1.6	1.00	0.6
36694.W2512-B4	M 2.5	12	1.7	3.7	4.5	2.8	1.6	1.00	0.6
36694.W2516-B4	M 2.5	16	1.7	3.7	4.5	2.8	1.6	1.00	0.6
36694.W2520-B4	M 2.5	20	1.7	3.7	4.5	2.8	1.6	1.00	0.6
36694.W2525-B4	M 2.5	25	1.7	3.7	4.5	2.8	1.6	1.00	0.6
36694.W2530-B4	M 2.5	30	1.7	3.7	4.5	2.8	1.6	1.00	0.6
36694.W3006-B4	M 3	6	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3008-B4	M 3	8	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3010-B4	M 3	10	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3011-B4	M 3	11	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3013-B4	M 3	13	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3016-B4	M 3	16	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3018-B4	M 3	18	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3020-B4	M 3	20	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3025-B4	M 3	25	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3030-B4	M 3	30	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3040-B4	M 3	40	2.0	4.5	5.5	3.5	2.0	1.30	0.8
36694.W3510-B4	M 3.5	10	2.3	5.2	6.0	3.8	2.4	1.40	1.0
36694.W3516-B4	M 3.5	16	2.3	5.2	6.0	3.8	2.4	1.40	1.0
36694.W3520-B4	M 3.5	20	2.3	5.2	6.0	3.8	2.4	1.40	1.0
36694.W3525-B4	M 3.5	25	2.3	5.2	6.0	3.8	2.4	1.40	1.0



Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	l ₂ ±0.25	d ₃	d ₄ min.	h ₁	h ₂	w ₁
36694.W3530-B4	M 3.5	30	2.3	5.2	6.0	3.8	2.4	1.40	1.0
36694.W3540-B4	M 3.5	40	2.3	5.2	6.0	3.8	2.4	1.40	1.0
36694.W4010-B4	M 4	10	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4012-B4	M 4	12	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4016-B4	M 4	16	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4018-B4	M 4	18	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4019-B4	M 4	19	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4020-B4	M 4	20	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4025-B4	M 4	25	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4030-B4	M 4	30	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4040-B4	M 4	40	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4050-B4	M 4	50	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W4060-B4	M 4	60	2.8	6.0	7.0	4.5	2.6	1.60	1.2
36694.W5010-B4	M 5	10	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5012-B4	M 5	12	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5016-B4	M 5	16	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5018-B4	M 5	18	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5020-B4	M 5	20	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5022-B4	M 5	22	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5025-B4	M 5	25	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5030-B4	M 5	30	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5040-B4	M 5	40	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5050-B4	M 5	50	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5060-B4	M 5	60	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W5080-B4	M 5	80	3.7	7.5	8.5	5.5	3.3	2.00	1.2
36694.W6010-B4	M 6	10	4.2	7.5	10.0	6.5	3.9	2.30	1.6
36694.W6012-B4	M 6	12	4.2	7.5	10.0	6.5	3.9	2.30	1.6
36694.W6016-B4	M 6	16	4.2	7.5	10.0	6.5	3.9	2.30	1.6
36694.W6020-B4	M 6	20	4.2	7.5	10.0	6.5	3.9	2.30	1.6
36694.W6025-B4	M 6	25	4.2	7.5	10.0	6.5	3.9	2.30	1.6
36694.W6030-B4	M 6	30	4.2	7.5	10.0	6.5	3.9	2.30	1.6
36694.W6040-B4	M 6	40	4.2	7.5	10.0	6.5	3.9	2.30	1.6
36694.W6050-B4	M 6	50	4.2	7.5	10.0	6.5	3.9	2.30	1.6
36694.W6060-B4	M 6	60	4.2	7.5	10.0	6.5	3.9	2.30	1.6
36694.W6080-B4	M 6	80	4.2	7.5	10.0	6.5	3.9	2.30	1.6