




Shoulder Screws - Countersunk

hex drive - 303 stainless

Shoulder Screws



33666.A2

SHOULDER SCREWS

Material

Stainless steel (AISI 303, 1.4305).
Tensile strength 550 N/mm².
Proof stress min. 190 N/mm², austenitic

stainless steel.

Technical Notes

303 stainless steel provides good resi-

stance to corrosion. It is mildly magnetic.
Special lengths and diameters produced to
drawings.

Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2 tol. G6	d_3	l_2 +0.05 -0.00	h_1 +0.00 -0.05	A/F
33666.W0410-A2	4	10	M 3	8	4	2.0	2.0
33666.W0412-A2	4	12	M 3	8	4	2.0	2.0
33666.W0414-A2	4	14	M 3	8	4	2.0	2.0
33666.W0416-A2	4	16	M 3	8	4	2.0	2.0
33666.W0418-A2	4	18	M 3	8	4	2.0	2.0
33666.W0420-A2	4	20	M 3	8	4	2.0	2.0
33666.W0425-A2	4	25	M 3	8	4	2.0	2.0
33666.W0430-A2	4	30	M 3	8	4	2.0	2.0
33666.W0510-A2	5	10	M 4	10	5	2.5	2.5
33666.W0512-A2	5	12	M 4	10	5	2.5	2.5
33666.W0516-A2	5	16	M 4	10	5	2.5	2.5
33666.W0520-A2	5	20	M 4	10	5	2.5	2.5
33666.W0525-A2	5	25	M 4	10	5	2.5	2.5
33666.W0530-A2	5	30	M 4	10	5	2.5	2.5
33666.W0535-A2	5	35	M 4	10	5	2.5	2.5
33666.W0540-A2	5	40	M 4	10	5	2.5	2.5
33666.W0610-A2	6	10	M 5	12	6	3.0	3.0
33666.W0612-A2	6	12	M 5	12	6	3.0	3.0
33666.W0616-A2	6	16	M 5	12	6	3.0	3.0
33666.W0620-A2	6	20	M 5	12	6	3.0	3.0
33666.W0625-A2	6	25	M 5	12	6	3.0	3.0
33666.W0630-A2	6	30	M 5	12	6	3.0	3.0
33666.W0635-A2	6	35	M 5	12	6	3.0	3.0
33666.W0640-A2	6	40	M 5	12	6	3.0	3.0
33666.W0810-A2	8	10	M 6	16	11	4.0	4.0
33666.W0812-A2	8	12	M 6	16	11	4.0	4.0
33666.W0816-A2	8	16	M 6	16	11	4.0	4.0
33666.W0820-A2	8	20	M 6	16	11	4.0	4.0
33666.W0825-A2	8	25	M 6	16	11	4.0	4.0
33666.W0830-A2	8	30	M 6	16	11	4.0	4.0
33666.W0835-A2	8	35	M 6	16	11	4.0	4.0
33666.W0840-A2	8	40	M 6	16	11	4.0	4.0
33666.W1012-A2	10	12	M 8	20	12	5.0	5.0
33666.W1016-A2	10	16	M 8	20	12	5.0	5.0



Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2 tol. G6	d_3	l_2 +0.05 -0.00	h_1 +0.00 -0.05	A/F
33666.W1020-A2	10	20	M 8	20	12	5.0	5.0
33666.W1025-A2	10	25	M 8	20	12	5.0	5.0
33666.W1030-A2	10	30	M 8	20	12	5.0	5.0
33666.W1040-A2	10	40	M 8	20	12	5.0	5.0
33666.W1050-A2	10	50	M 8	20	12	5.0	5.0
33666.W1212-A2	12	12	M 10	24	16	6.0	6.0
33666.W1216-A2	12	16	M 10	24	16	6.0	6.0
33666.W1220-A2	12	20	M 10	24	16	6.0	6.0
33666.W1225-A2	12	25	M 10	24	16	6.0	6.0
33666.W1230-A2	12	30	M 10	24	16	6.0	6.0
33666.W1240-A2	12	40	M 10	24	16	6.0	6.0
33666.W1250-A2	12	50	M 10	24	16	6.0	6.0