



Shoulder Screws - Countersunk


hex drive - 316 stainless

Shoulder Screws



33666.A4

SHOULDER SCREWS



Material

Stainless steel (AISI 316, 1.440).
Tensile strength 480 N/mm².
Proof stress min. 200 N/mm², austenitic stainless steel.

Technical Notes

316 Stainless provides excellent corrosion resistance for use in highly caustic or marine environments. For more standard applications please see our A2 range which

is more cost effective.
Non-magnetic.

Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2 tol. G6	d_3	l_2 +0.05 -0.00	h_1 +0.00 -0.05	A/F
33666.W0410-A4	4	10	M 3	8	4	2.0	2.0
33666.W0412-A4	4	12	M 3	8	4	2.0	2.0
33666.W0414-A4	4	14	M 3	8	4	2.0	2.0
33666.W0416-A4	4	16	M 3	8	4	2.0	2.0
33666.W0418-A4	4	18	M 3	8	4	2.0	2.0
33666.W0420-A4	4	20	M 3	8	4	2.0	2.0
33666.W0425-A4	4	25	M 3	8	4	2.0	2.0
33666.W0430-A4	4	30	M 3	8	4	2.0	2.0
33666.W0510-A4	5	10	M 4	10	5	2.5	2.5
33666.W0512-A4	5	12	M 4	10	5	2.5	2.5
33666.W0516-A4	5	16	M 4	10	5	2.5	2.5
33666.W0520-A4	5	20	M 4	10	5	2.5	2.5
33666.W0525-A4	5	25	M 4	10	5	2.5	2.5
33666.W0530-A4	5	30	M 4	10	5	2.5	2.5
33666.W0535-A4	5	35	M 4	10	5	2.5	2.5
33666.W0540-A4	5	40	M 4	10	5	2.5	2.5
33666.W0610-A4	6	10	M 5	12	6	3.0	3.0
33666.W0612-A4	6	12	M 5	12	6	3.0	3.0
33666.W0616-A4	6	16	M 5	12	6	3.0	3.0
33666.W0620-A4	6	20	M 5	12	6	3.0	3.0
33666.W0625-A4	6	25	M 5	12	6	3.0	3.0
33666.W0630-A4	6	30	M 5	12	6	3.0	3.0
33666.W0635-A4	6	35	M 5	12	6	3.0	3.0
33666.W0640-A4	6	40	M 5	12	6	3.0	3.0
33666.W0810-A4	8	10	M 6	16	11	4.0	4.0
33666.W0812-A4	8	12	M 6	16	11	4.0	4.0
33666.W0816-A4	8	16	M 6	16	11	4.0	4.0
33666.W0820-A4	8	20	M 6	16	11	4.0	4.0
33666.W0825-A4	8	25	M 6	16	11	4.0	4.0
33666.W0830-A4	8	30	M 6	16	11	4.0	4.0
33666.W0835-A4	8	35	M 6	16	11	4.0	4.0
33666.W0840-A4	8	40	M 6	16	11	4.0	4.0
33666.W1012-A4	10	12	M 8	20	12	5.0	5.0



Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2 tol. G6	d_3	l_2 +0.05 -0.00	h_1 +0.00 -0.05	A/F
33666.W1016-A4	10	16	M 8	20	12	5.0	5.0
33666.W1020-A4	10	20	M 8	20	12	5.0	5.0
33666.W1025-A4	10	25	M 8	20	12	5.0	5.0
33666.W1030-A4	10	30	M 8	20	12	5.0	5.0
33666.W1040-A4	10	40	M 8	20	12	5.0	5.0
33666.W1050-A4	10	50	M 8	20	12	5.0	5.0
33666.W1212-A4	12	12	M 10	24	16	6.0	6.0
33666.W1216-A4	12	16	M 10	24	16	6.0	6.0
33666.W1220-A4	12	20	M 10	24	16	6.0	6.0
33666.W1225-A4	12	25	M 10	24	16	6.0	6.0
33666.W1230-A4	12	30	M 10	24	16	6.0	6.0
33666.W1240-A4	12	40	M 10	24	16	6.0	6.0
33666.W1250-A4	12	50	M 10	24	16	6.0	6.0