


Captive Panel Thumb Screws

slot drive - 316 stainless


Captive Screws



36698.A4



application examples :-
counterbore length 'x₁' should be > l₂



threaded
captive washer

Material

Stainless steel (AISI 316, 1.440).
Tensile strength 480 N/mm². Proof stress
min. 200 N/mm², austenitic stainless steel.
Also available on request in steel
(anodised, black oxide or zinc plated),

stainless steel (AISI 303, 1.4305), brass,
aluminium etc.

Technical Notes

Used to comply with the Machinery Direc-
tive 2006/42/EC. Often used with our

captive washers (36691) or retaining
flanges (36692 - for sheet metal applica-
tions). The use of our captive washers
should be considered when fitted in panels
with unthreaded holes.

Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	d ₃	d ₄ min.	h ₁	h ₂	l ₂ ±0.25	l ₃	l ₄	w ₁
36698.W3010-A4	M 3	10	2.0	6.5	3.5	6.5	2.0	3.2	4.8	2.0	1.2
36698.W3014-A4	M 3	14	2.0	6.5	3.5	6.5	2.0	3.2	8.8	2.0	1.2
36698.W3016-A4	M 3	16	2.0	6.5	3.5	6.5	2.0	3.2	10.8	2.0	1.2
36698.W3020-A4	M 3	20	2.0	6.5	3.5	6.5	2.0	3.2	14.8	2.0	1.2
36698.W3022-A4	M 3	22	2.0	6.5	3.5	6.5	2.0	3.2	16.8	2.0	1.2
36698.W3024-A4	M 3	24	2.0	6.5	3.5	6.5	2.0	3.2	18.8	2.0	1.2
36698.W3026-A4	M 3	26	2.0	6.5	3.5	6.5	2.0	3.2	20.8	2.0	1.2
36698.W3110-A4	M 3	10	2.0	8.0	3.5	8.0	2.0	3.2	4.8	2.0	1.2
36698.W3114-A4	M 3	14	2.0	8.0	3.5	8.0	2.0	3.2	8.8	2.0	1.2
36698.W3116-A4	M 3	16	2.0	8.0	3.5	8.0	2.0	3.2	10.8	2.0	1.2
36698.W3120-A4	M 3	20	2.0	8.0	3.5	8.0	2.0	3.2	14.8	2.0	1.2
36698.W3122-A4	M 3	22	2.0	8.0	3.5	8.0	2.0	3.2	16.8	2.0	1.2
36698.W3124-A4	M 3	24	2.0	8.0	3.5	8.0	2.0	3.2	18.8	2.0	1.2
36698.W4010-A4	M 4	10	3.0	8.0	4.5	8.0	2.0	5.5	2.0	2.5	1.2
36698.W4014-A4	M 4	14	3.0	8.0	4.5	8.0	2.0	5.5	6.0	2.5	1.2
36698.W4016-A4	M 4	16	3.0	8.0	4.5	8.0	2.0	5.5	8.0	2.5	1.2
36698.W4020-A4	M 4	20	3.0	8.0	4.5	8.0	2.0	5.5	12.0	2.5	1.2
36698.W4022-A4	M 4	22	3.0	8.0	4.5	8.0	2.0	5.5	14.0	2.5	1.2
36698.W4024-A4	M 4	24	3.0	8.0	4.5	8.0	2.0	5.5	16.0	2.5	1.2
36698.W4027-A4	M 4	27	3.0	8.0	4.5	8.0	2.0	5.5	19.0	2.5	1.2
36698.W4032-A4	M 4	32	3.0	8.0	4.5	8.0	2.0	5.5	24.0	2.5	1.2
36698.W5014-A4	M 5	14	3.5	10.0	5.5	10.0	2.5	6.5	3.5	4.0	1.5
36698.W5016-A4	M 5	16	3.5	10.0	5.5	10.0	2.5	6.5	5.5	4.0	1.5
36698.W5020-A4	M 5	20	3.5	10.0	5.5	10.0	2.5	6.5	9.5	4.0	1.5
36698.W5022-A4	M 5	22	3.5	10.0	5.5	10.0	2.5	6.5	11.5	4.0	1.5
36698.W5024-A4	M 5	24	3.5	10.0	5.5	10.0	2.5	6.5	13.5	4.0	1.5
36698.W5027-A4	M 5	27	3.5	10.0	5.5	10.0	2.5	6.5	16.5	4.0	1.5
36698.W5032-A4	M 5	32	3.5	10.0	5.5	10.0	2.5	6.5	21.5	4.0	1.5
36698.W5035-A4	M 5	35	3.5	10.0	5.5	10.0	2.5	6.5	24.5	4.0	1.5
36698.W5040-A4	M 5	40	3.5	10.0	5.5	10.0	2.5	6.5	29.5	4.0	1.5
36698.W6016-A4	M 6	16	4.5	12.0	6.5	15.0	2.5	8.0	3.0	5.0	2.0
36698.W6020-A4	M 6	20	4.5	12.0	6.5	15.0	2.5	8.0	7.0	5.0	2.0



Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	d ₃	d ₄ min.	h ₁	h ₂	l ₂ ±0.25	l ₃	l ₄	w ₁
36698.W6022-A4	M 6	22	4.5	12.0	6.5	15.0	2.5	8.0	9.0	5.0	2.0
36698.W6024-A4	M 6	24	4.5	12.0	6.5	15.0	2.5	8.0	11.0	5.0	2.0
36698.W6027-A4	M 6	27	4.5	12.0	6.5	15.0	2.5	8.0	14.0	5.0	2.0
36698.W6032-A4	M 6	32	4.5	12.0	6.5	15.0	2.5	8.0	19.0	5.0	2.0
36698.W6035-A4	M 6	35	4.5	12.0	6.5	15.0	2.5	8.0	22.0	5.0	2.0
36698.W6040-A4	M 6	40	4.5	12.0	6.5	15.0	2.5	8.0	27.0	8.5	2.0
36698.W6045-A4	M 6	45	4.5	12.0	6.5	15.0	2.5	8.0	32.0	8.5	2.0
36698.W6050-A4	M 6	50	4.5	12.0	6.5	15.0	2.5	8.0	37.0	8.5	2.0