





Captive Panel Thumb Screws

slot drive - titanium

Captive Screws



application examples :-
counterbore length 'x₁' should be > l₂



36698.Ti

CAPTIVE SCREWS

Material

Titanium grade 2 (tensile strength 345 N/mm²), or grade 5 (tensile strength 900 N/mm²).

Also available on request in steel (anodised, black oxide or zinc plated) stainless steel (AISI 316, 1.440 or AISI

303, 1.4305), brass, aluminium etc.

Technical Notes

Used to comply with the Machinery Directive 2006/42/EC. Often used with our captive washer (36691) or retaining flanges (36692 - for sheet metal applica-

tions). The use of our captive washer should be considered when fitted in panels with unthreaded holes.

T5 also available on request.

Replace -T2 with -T5 at the end of part number.

Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	l ₂ ±0.25	d ₃	d ₄ min.	h ₁	h ₂	l ₃	l ₄	w ₁	Material
36698.W3010-T2	M 3	10	2.0	3.2	6.5	3.5	6.5	2.0	4.8	2.0	1.2	Grade 2
36698.W3014-T2	M 3	14	2.0	3.2	6.5	3.5	6.5	2.0	8.8	2.0	1.2	Grade 2
36698.W3016-T2	M 3	16	2.0	3.2	6.5	3.5	6.5	2.0	10.8	2.0	1.2	Grade 2
36698.W3020-T2	M 3	20	2.0	3.2	6.5	3.5	6.5	2.0	14.8	2.0	1.2	Grade 2
36698.W3022-T2	M 3	22	2.0	3.2	6.5	3.5	6.5	2.0	16.8	2.0	1.2	Grade 2
36698.W3024-T2	M 3	24	2.0	3.2	6.5	3.5	6.5	2.0	18.8	2.0	1.2	Grade 2
36698.W3026-T2	M 3	26	2.0	3.2	6.5	3.5	6.5	2.0	20.8	2.0	1.2	Grade 2
36698.W3110-T2	M 3	10	2.0	3.2	8.0	3.5	8.0	2.0	4.8	2.0	1.2	Grade 2
36698.W3114-T2	M 3	14	2.0	3.2	8.0	3.5	8.0	2.0	8.8	2.0	1.2	Grade 2
36698.W3116-T2	M 3	16	2.0	3.2	8.0	3.5	8.0	2.0	10.8	2.0	1.2	Grade 2
36698.W3120-T2	M 3	20	2.0	3.2	8.0	3.5	8.0	2.0	14.8	2.0	1.2	Grade 2
36698.W3122-T2	M 3	22	2.0	3.2	8.0	3.5	8.0	2.0	16.8	2.0	1.2	Grade 2
36698.W3124-T2	M 3	24	2.0	3.2	8.0	3.5	8.0	2.0	18.8	2.0	1.2	Grade 2
36698.W4010-T2	M 4	10	3.0	5.5	8.0	4.5	8.0	2.0	2.0	2.5	1.2	Grade 2
36698.W4014-T2	M 4	14	3.0	5.5	8.0	4.5	8.0	2.0	6.0	2.5	1.2	Grade 2
36698.W4016-T2	M 4	16	3.0	5.5	8.0	4.5	8.0	2.0	8.0	2.5	1.2	Grade 2
36698.W4020-T2	M 4	20	3.0	5.5	8.0	4.5	8.0	2.0	12.0	2.5	1.2	Grade 2
36698.W4022-T2	M 4	22	3.0	5.5	8.0	4.5	8.0	2.0	14.0	2.5	1.2	Grade 2
36698.W4024-T2	M 4	24	3.0	5.5	8.0	4.5	8.0	2.0	16.0	2.5	1.2	Grade 2
36698.W4027-T2	M 4	27	3.0	5.5	8.0	4.5	8.0	2.0	19.0	2.5	1.2	Grade 2
36698.W4032-T2	M 4	32	3.0	5.5	8.0	4.5	8.0	2.0	24.0	2.5	1.2	Grade 2
36698.W5014-T2	M 5	14	3.5	6.5	10.0	5.5	10.0	2.5	3.5	4.0	1.5	Grade 2
36698.W5016-T2	M 5	16	3.5	6.5	10.0	5.5	10.0	2.5	5.5	4.0	1.5	Grade 2
36698.W5020-T2	M 5	20	3.5	6.5	10.0	5.5	10.0	2.5	9.5	4.0	1.5	Grade 2
36698.W5022-T2	M 5	22	3.5	6.5	10.0	5.5	10.0	2.5	11.5	4.0	1.5	Grade 2
36698.W5024-T2	M 5	24	3.5	6.5	10.0	5.5	10.0	2.5	13.5	4.0	1.5	Grade 2
36698.W5027-T2	M 5	27	3.5	6.5	10.0	5.5	10.0	2.5	16.5	4.0	1.5	Grade 2
36698.W5032-T2	M 5	32	3.5	6.5	10.0	5.5	10.0	2.5	21.5	4.0	1.5	Grade 2
36698.W5035-T2	M 5	35	3.5	6.5	10.0	5.5	10.0	2.5	24.5	4.0	1.5	Grade 2
36698.W5040-T2	M 5	40	3.5	6.5	10.0	5.5	10.0	2.5	29.5	4.0	1.5	Grade 2
36698.W6016-T2	M 6	16	4.5	8.0	12.0	6.5	15.0	2.5	3.0	5.0	2.0	Grade 2



Order No.	d ₁	l ₁ ±0.25	d ₂ ±0.12	l ₂ ±0.25	d ₃	d ₄ min.	h ₁	h ₂	l ₃	l ₄	w ₁	Material
36698.W6020-T2	M 6	20	4.5	8.0	12.0	6.5	15.0	2.5	7.0	5.0	2.0	Grade 2
36698.W6022-T2	M 6	22	4.5	8.0	12.0	6.5	15.0	2.5	9.0	5.0	2.0	Grade 2
36698.W6024-T2	M 6	24	4.5	8.0	12.0	6.5	15.0	2.5	11.0	5.0	2.0	Grade 2
36698.W6027-T2	M 6	27	4.5	8.0	12.0	6.5	15.0	2.5	14.0	5.0	2.0	Grade 2
36698.W6032-T2	M 6	32	4.5	8.0	12.0	6.5	15.0	2.5	19.0	5.0	2.0	Grade 2
36698.W6035-T2	M 6	35	4.5	8.0	12.0	6.5	15.0	2.5	22.0	5.0	2.0	Grade 2
36698.W6040-T2	M 6	40	4.5	8.0	12.0	6.5	15.0	2.5	27.0	8.5	2.0	Grade 2
36698.W6045-T2	M 6	45	4.5	8.0	12.0	6.5	15.0	2.5	32.0	8.5	2.0	Grade 2
36698.W6050-T2	M 6	50	4.5	8.0	12.0	6.5	15.0	2.5	37.0	8.5	2.0	Grade 2
36698.W3010-T5	M 3	10	2.0	3.2	6.5	3.5	6.5	2.0	4.8	2.0	1.2	Grade 5
36698.W3014-T5	M 3	14	2.0	3.2	6.5	3.5	6.5	2.0	8.8	2.0	1.2	Grade 5
36698.W3016-T5	M 3	16	2.0	3.2	6.5	3.5	6.5	2.0	10.8	2.0	1.2	Grade 5
36698.W3020-T5	M 3	20	2.0	3.2	6.5	3.5	6.5	2.0	14.8	2.0	1.2	Grade 5
36698.W3022-T5	M 3	22	2.0	3.2	6.5	3.5	6.5	2.0	16.8	2.0	1.2	Grade 5
36698.W3024-T5	M 3	24	2.0	3.2	6.5	3.5	6.5	2.0	18.8	2.0	1.2	Grade 5
36698.W3026-T5	M 3	26	2.0	3.2	6.5	3.5	6.5	2.0	20.8	2.0	1.2	Grade 5
36698.W3110-T5	M 3	10	2.0	3.2	8.0	3.5	8.0	2.0	4.8	2.0	1.2	Grade 5
36698.W3114-T5	M 3	14	2.0	3.2	8.0	3.5	8.0	2.0	8.8	2.0	1.2	Grade 5
36698.W3116-T5	M 3	16	2.0	3.2	8.0	3.5	8.0	2.0	10.8	2.0	1.2	Grade 5
36698.W3120-T5	M 3	20	2.0	3.2	8.0	3.5	8.0	2.0	14.8	2.0	1.2	Grade 5
36698.W3122-T5	M 3	22	2.0	3.2	8.0	3.5	8.0	2.0	16.8	2.0	1.2	Grade 5
36698.W3124-T5	M 3	24	2.0	3.2	8.0	3.5	8.0	2.0	18.8	2.0	1.2	Grade 5
36698.W4010-T5	M 4	10	3.0	5.5	8.0	4.5	8.0	2.0	2.0	2.5	1.2	Grade 5
36698.W4014-T5	M 4	14	3.0	5.5	8.0	4.5	8.0	2.0	6.0	2.5	1.2	Grade 5
36698.W4016-T5	M 4	16	3.0	5.5	8.0	4.5	8.0	2.0	8.0	2.5	1.2	Grade 5
36698.W4020-T5	M 4	20	3.0	5.5	8.0	4.5	8.0	2.0	12.0	2.5	1.2	Grade 5
36698.W4022-T5	M 4	22	3.0	5.5	8.0	4.5	8.0	2.0	14.0	2.5	1.2	Grade 5
36698.W4024-T5	M 4	24	3.0	5.5	8.0	4.5	8.0	2.0	16.0	2.5	1.2	Grade 5
36698.W4027-T5	M 4	27	3.0	5.5	8.0	4.5	8.0	2.0	19.0	2.5	1.2	Grade 5
36698.W4032-T5	M 4	32	3.0	5.5	8.0	4.5	8.0	2.0	24.0	2.5	1.2	Grade 5
36698.W5014-T5	M 5	14	3.5	6.5	10.0	5.5	10.0	2.5	3.5	4.0	1.5	Grade 5
36698.W5016-T5	M 5	16	3.5	6.5	10.0	5.5	10.0	2.5	5.5	4.0	1.5	Grade 5
36698.W5020-T5	M 5	20	3.5	6.5	10.0	5.5	10.0	2.5	9.5	4.0	1.5	Grade 5
36698.W5022-T5	M 5	22	3.5	6.5	10.0	5.5	10.0	2.5	11.5	4.0	1.5	Grade 5
36698.W5024-T5	M 5	24	3.5	6.5	10.0	5.5	10.0	2.5	13.5	4.0	1.5	Grade 5
36698.W5027-T5	M 5	27	3.5	6.5	10.0	5.5	10.0	2.5	16.5	4.0	1.5	Grade 5
36698.W5032-T5	M 5	32	3.5	6.5	10.0	5.5	10.0	2.5	21.5	4.0	1.5	Grade 5
36698.W5035-T5	M 5	35	3.5	6.5	10.0	5.5	10.0	2.5	24.5	4.0	1.5	Grade 5
36698.W5040-T5	M 5	40	3.5	6.5	10.0	5.5	10.0	2.5	29.5	4.0	1.5	Grade 5
36698.W6016-T5	M 6	16	4.5	8.0	12.0	6.5	15.0	2.5	3.0	5.0	2.0	Grade 5
36698.W6020-T5	M 6	20	4.5	8.0	12.0	6.5	15.0	2.5	7.0	5.0	2.0	Grade 5
36698.W6022-T5	M 6	22	4.5	8.0	12.0	6.5	15.0	2.5	9.0	5.0	2.0	Grade 5
36698.W6024-T5	M 6	24	4.5	8.0	12.0	6.5	15.0	2.5	11.0	5.0	2.0	Grade 5
36698.W6027-T5	M 6	27	4.5	8.0	12.0	6.5	15.0	2.5	14.0	5.0	2.0	Grade 5
36698.W6032-T5	M 6	32	4.5	8.0	12.0	6.5	15.0	2.5	19.0	5.0	2.0	Grade 5
36698.W6035-T5	M 6	35	4.5	8.0	12.0	6.5	15.0	2.5	22.0	5.0	2.0	Grade 5
36698.W6040-T5	M 6	40	4.5	8.0	12.0	6.5	15.0	2.5	27.0	8.5	2.0	Grade 5
36698.W6045-T5	M 6	45	4.5	8.0	12.0	6.5	15.0	2.5	32.0	8.5	2.0	Grade 5
36698.W6050-T5	M 6	50	4.5	8.0	12.0	6.5	15.0	2.5	37.0	8.5	2.0	Grade 5