



Shoulder Screws - Countersunk

hex drive - 303 stainless - blackened


Shoulder Screws



MADE IN
BRITAIN

33666.B2

SHOULDER SCREWS



Material

Stainless steel (AISI 303, 1.4305),
blackened.

Tensile strength 550 N/mm².

Proof stress min. 190 N/mm², austenitic

stainless steel.


Technical Notes

303 stainless steel provides good resistance to corrosion, it is soft and mildly

magnetic.

Blackening provides some further corrosion resistance

Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2 tol. G6	d_3	l_2 +0.05 -0.00	h_1 +0.00 -0.05	A/F
33666.W0410-B2	4	10	M 3	8	4	2.0	2.0
33666.W0412-B2	4	12	M 3	8	4	2.0	2.0
33666.W0414-B2	4	14	M 3	8	4	2.0	2.0
33666.W0416-B2	4	16	M 3	8	4	2.0	2.0
33666.W0418-B2	4	18	M 3	8	4	2.0	2.0
33666.W0420-B2	4	20	M 3	8	4	2.0	2.0
33666.W0425-B2	4	25	M 3	8	4	2.0	2.0
33666.W0430-B2	4	30	M 3	8	4	2.0	2.0
33666.W0510-B2	5	10	M 4	10	5	2.5	2.5
33666.W0512-B2	5	12	M 4	10	5	2.5	2.5
33666.W0516-B2	5	16	M 4	10	5	2.5	2.5
33666.W0520-B2	5	20	M 4	10	5	2.5	2.5
33666.W0525-B2	5	25	M 4	10	5	2.5	2.5
33666.W0530-B2	5	30	M 4	10	5	2.5	2.5
33666.W0535-B2	5	35	M 4	10	5	2.5	2.5
33666.W0540-B2	5	40	M 4	10	5	2.5	2.5
33666.W0610-B2	6	10	M 5	12	6	3.0	3.0
33666.W0612-B2	6	12	M 5	12	6	3.0	3.0
33666.W0616-B2	6	16	M 5	12	6	3.0	3.0
33666.W0620-B2	6	20	M 5	12	6	3.0	3.0
33666.W0625-B2	6	25	M 5	12	6	3.0	3.0
33666.W0630-B2	6	30	M 5	12	6	3.0	3.0
33666.W0635-B2	6	35	M 5	12	6	3.0	3.0
33666.W0640-B2	6	40	M 5	12	6	3.0	3.0
33666.W0810-B2	8	10	M 6	16	11	4.0	4.0
33666.W0812-B2	8	12	M 6	16	11	4.0	4.0
33666.W0816-B2	8	16	M 6	16	11	4.0	4.0
33666.W0820-B2	8	20	M 6	16	11	4.0	4.0
33666.W0825-B2	8	25	M 6	16	11	4.0	4.0
33666.W0830-B2	8	30	M 6	16	11	4.0	4.0
33666.W0835-B2	8	35	M 6	16	11	4.0	4.0
33666.W0840-B2	8	40	M 6	16	11	4.0	4.0
33666.W1012-B2	10	12	M 8	20	12	5.0	5.0



Order No.	d_1 +0.000 -0.025	l_1 +0.05 -0.00	d_2 tol. G6	d_3	l_2 +0.05 -0.00	h_1 +0.00 -0.05	A/F
33666.W1016-B2	10	16	M 8	20	12	5.0	5.0
33666.W1020-B2	10	20	M 8	20	12	5.0	5.0
33666.W1025-B2	10	25	M 8	20	12	5.0	5.0
33666.W1030-B2	10	30	M 8	20	12	5.0	5.0
33666.W1040-B2	10	40	M 8	20	12	5.0	5.0
33666.W1050-B2	10	50	M 8	20	12	5.0	5.0
33666.W1212-B2	12	12	M 10	24	16	6.0	6.0
33666.W1216-B2	12	16	M 10	24	16	6.0	6.0
33666.W1220-B2	12	20	M 10	24	16	6.0	6.0
33666.W1225-B2	12	25	M 10	24	16	6.0	6.0
33666.W1230-B2	12	30	M 10	24	16	6.0	6.0
33666.W1240-B2	12	40	M 10	24	16	6.0	6.0
33666.W1250-B2	12	50	M 10	24	16	6.0	6.0