




Fixed Feet non-tilt

Levelling Feet



34620

LEVELLING FEET

Material

Thread: steel, zinc plated.

Pad: thermoplastic, black.

Order No.	d ₁	d ₂	l	c	b	a
34620.W0020	M 8	25	17	18	8	2
34620.W0021	M 8	25	22	18	8	2
34620.W0022	M 8	25	27	18	8	2
34620.W0031	M 8	30	27	18	8	2
34620.W0042	M 8	40	32	20	9	2
34620.W0045	M10	40	22	20	9	2
34620.W0046	M10	40	32	20	9	2
34620.W0056	M10	50	32	22	10	2
34620.W0065	M10	60	37	22	10	2
34620.W0066	M10	60	27	22	10	2
34620.W0085	M10	80	22	26	10	2
34620.W0086	M10	80	32	26	10	2
34620.W0087	M10	80	37	26	10	2




A Range of features to suit your application

Product selection

To ensure you select the most suitable levelling feet for your application consider the following questions:

- Tilting or fixed?
- Material required - steel, stainless or plastic?
- Load carrying capacity - light, medium or heavy duty?
(Review the quoted load capacities in the individual product tables).
- Bolt down feature required?
- Threaded or plastic insert required for mounting?
- Optional extras: hygiene seal, rubber pad, (subject to minimum quantity and selected model).

Key types



Fixed feet



Articulating levelling foot




Machine mounts



Fulcrum screw

Available features



Articulation



Standard nylon base




Anti-slip base



Bolt down base



Hygienic seal



Hex for easy installation

Materials



Steel thread - Nylon base



Stainless thread - Nylon base




Steel thread - Steel base



Stainless thread - Stainless base


Mounting inserts



Weldable insert



Hollow section insert



Hollow section bushed insert

Additional technical information



▶ For applications under greater loads and requiring increased precision of adjustment see our range of Precision Height Adjusters.

▶ For applications exposed to extreme vibrations see our range of Anti-Vibration Mounts.

