





34910

Material

Steel body with zinc plated thread.
Synthetic rubber base (65 Shore A), with
anti-slide cavity.

Technical Notes

Suitable for medium and high frequency

vibrations and with smooth floors.

Tips

For inclined floors use the swivel base
versions (M12 and M16).

The swivel base versions have a separate
screw which rests in the concave cup on the

top portion of the foot body.

Order No.	Style	d ₁	h ₁	d ₂	l ₁	Load range kgf
34910.W0040	Fixed	40	15	M 8	40	0-60
34910.W0063	Fixed	63	18	M10	83	30-100
34910.W0070	Fixed	70	22	M12	90	80-150
34910.W0090	Fixed	90	25	M12	90	100-350
34910.W0106	Fixed	106	29	M16	110	300-600
34910.W0127	Fixed	127	33	M16	110	500-900
34910.W0150	Fixed	150	39	M16	110	800-1500
34910.W0170	Fixed	170	42	M16	110	1300-2000
34910.W0370	Swivel	70	22	M12	90	80-150
34910.W0390	Swivel	90	26	M12	90	100-350
34910.W0406	Swivel	106	32	M16	110	300-600
34910.W0427	Swivel	127	33	M16	110	500-900
34910.W0450	Swivel	150	39	M16	110	800-1500
34910.W0470	Swivel	170	42	M16	110	1300-2000