




Grippers - Carbide Tipped threaded bolt

Grippers & Rest Pads



35400

GRIPPERS & REST PADS

Material

Hex headed steel bolt with solid carbide tipped insert.

used in jigs and fixtures, modular fixtures and tooling. They are especially suitable for holding castings and other components. Adjustment can be made within the thread length. Use a DIN 439B

hex. nut for adjustment and securing.


Technical Notes

Adjustable carbide tipped grippers are

Order No.	Tooth pattern	d ₁	l ₁	l ₂	d ₂	w ₁	A/F
35400.W0001	Ex-fine	7.94	12	5.0	M 6x1,00	2,387x90°	10
35400.W0002	Ex-fine	7.94	25	5.0	M 6x1,00	2,387x90°	10
35400.W0003	Fine	9.53	12	6.4	M 8x1,25	3,175x90°	13
35400.W0004	Fine	9.53	25	6.4	M 8x1,25	3,175x90°	13
35400.W0005	Fine	9.53	35	6.4	M 8x1,25	3,175x90°	13
35400.W0006	Fine	12.70	12	7.5	M10x1,50	3,175x90°	17
35400.W0007	Fine	12.70	25	7.5	M10x1,50	3,175x90°	17
35400.W0008	Fine	12.70	40	7.5	M10x1,50	3,175x90°	17
35400.W0009	Fine	15.88	25	8.7	M12x1,75	3,175x90°	19
35400.W0010	Fine	15.88	40	8.7	M12x1,75	3,175x90°	19
35400.W0011	Fine	19.05	35	11.0	M16x2,00	3,175x90°	24
35400.W0012	Fine	19.05	50	11.0	M16x2,00	3,175x90°	24
35400.W0013	Ex-fine	25.40	40	13.7	M20x2,50	2,387x90°	30
35400.W0014	Ex-fine	25.40	60	13.7	M20x2,50	2,387x90°	30




Grippers enhance workholding for multiple machining operations.



Grippers increase handling capability.

Pads and Gripper Options

Pads



Solid Carbide

High impact carbide pads, can be brazed or bonded into place.



Carbide Tipped

Constructed with high impact carbide pad brazed to a heat treated alloy steel body. Mount via tapped hole or a flat on the outside diameter for set screw mounting.



Hardened Steel

Made from 8620 steel, carburized and hardened to Rc 58/60 1.2mm with black oxide finish. Mount via tapped or counter bored hole.




Non-marking Thermoplast

Made from white thermoplast. Mount via tapped or counter bored hole.



Stainless Steel

Pad from 17-4 stainless steel, hardened to Rc 43/46. Mount via tapped or counter bored hole.



Abrasive Diamond Surface

Abrasive surface permanently fused to a 17-4 stainless steel pad, hardened to Rc 43/46. The surface texture is comparable to a 100 grit abrasive. Mount via tapped or counter bored hole.



Soft Urethane Surface

Urethane surface is permanently bonded to a 300 series stainless steel pad. The urethane provides excellent protection against damage on delicate work surfaces. Tapped hole mounting.


see our website for our full range:
wixroyd.com

Grippers




High Speed Tool Steel

Manufactured from M-2 high speed tool steel, hardened to Rc 60/62 with black oxide finish. Mount via tapped hole, counter bored hole or a flat on the outside diameter for set screw mounting.




Carbide Tipped

Constructed with high impact carbide pad brazed to a heat treated alloy steel body. Mounts via tapped hole or a flat on the outside diameter for set screw mounting.





Solid Carbide

Manufactured from high impact carbide in a solid gripper pad or as a solid gripper body with a threaded brazed-in steel insert. Mount via tapped hole or a flat on the outside diameter for set screw mounting.




Tooth Pattern Specifications



Angular Grippers
 Our carbide and hardened steel grippers are available with a variety of tooth patterns, as specified on the product data tables.

Round/Square Grippers

Mounting options



Mounting Options for Carbide and Hardened Steel Grippers and Inserts.

Our carbide grippers and inserts can be installed in a number of different ways, the most suitable mounting method depends upon the specific insert – please refer to the product data table for specific information.

- 1 Round or square grippers and rest pads with tapped blind-hole or through hole tap.
- 2 Round or square grippers and rest pads with counter-bored hole.
- 3 Round grippers with flat on the O.D. for set screw mounting. Also square gripper mounting.
- 4 Round or square grippers with through tapped hole.
- 5 Round or square carbide pads.
- 6 Counter-bored edge grippers.

ov-W35300-A-T-W35520-A-T-technical-information-a-rmh - Updated - 28-10-2022



A Range of Specialist Gripping Pads to Suit Your Application

Urethane Coated



Unique urethane coat prevents marking of delicate components during machining or manipulation by robots. The urethane pad is permanently bonded to the stainless steel body of the gripping pad. With a bubbled texture, air is able to escape and hence avoid any suction action - enabling easy releasing of parts.

These are available in three different urethane durometers.



35 durometer:
Pencil rubber top




60 durometer:
Car tyre



80 durometer:
Skateboard wheel

Abrasive Diamond Coated



To improve handling of smooth or slippery components, with a minimum of clamping pressure, our abrasive diamond coated pads provide an excellent solution.

Diamond powders are permanently fused to a 17-4 stainless pad, to provide an abrasive surface comparable to 100 grit value.



Sandpaper of 100
grit texture

Stainless Pads



Pads of 17-4 Stainless, hardened to RC 43/46 provide solutions to applications where material selection is of greater importance; for example nuclear or food processing or pharmaceutical applications.