





# Threaded Rest Buttons male thread



**36401**

LOCATING PINS

### Material

Free-cutting steel, case-hardened and blackened. Thread not hardened.

### Technical Notes

The buttons are used as seats, stops and

thrust pads in jigs and fixtures as well as machine and equipment design. Dimension  $h_1$  tolerance of  $\pm 0,01$  for flat face type only, other types have  $h_1$  tolerance of  $\pm 0,1$ . Stated starting torque for female thread is

based on use of bolt of strength class 8 or greater and with full engagement of female thread.

### Tips

For female thread see 36402.

Order No.	Type	$d_1$	$d_2$	$d_3$	$h_1$	$h_2$	A/F	Torque to Nm max.	Weight g
36401.W0021	Flat Face	M 8	17	19.4	10	20	17	18	21
36401.W0031	Flat Face	M10	19	21.9	10	22	19	32	28
36401.W0032	Flat Face	M10	19	21.9	15	27	19	32	40
36401.W0001	Flat Face	M12	22	25.2	10	24	22	60	34
36401.W0002	Flat Face	M12	22	25.2	15	29	22	60	56
36401.W0042	Flat Face	M16	30	33.0	15	34	30	140	110
36401.W0043	Flat Face	M16	30	33.0	20	39	30	140	140
36401.W0052	Flat Face	M20	36	40.0	20	44	36	290	214
36401.W0053	Flat Face	M20	36	40.0	25	49	36	290	257
36401.W0062	Flat Face	M24	41	46.0	20	49	41	498	300
36401.W0063	Flat Face	M24	41	46.0	25	54	41	498	356
36401.W0064	Flat Face	M24	41	46.0	30	59	41	498	412
36401.W0121	Spherical Face	M 8	-	19.4	10	20	17	18	20
36401.W0131	Spherical Face	M10	-	21.9	10	22	19	32	30
36401.W0132	Spherical Face	M10	-	21.9	15	27	19	32	40
36401.W0101	Spherical Face	M12	-	25.2	10	24	22	60	38
36401.W0102	Spherical Face	M12	-	25.2	15	29	22	60	53
36401.W0142	Spherical Face	M16	-	33.0	15	34	30	140	105
36401.W0143	Spherical Face	M16	-	33.0	20	39	30	140	135
36401.W0152	Spherical Face	M20	-	40.0	20	44	36	290	206
36401.W0153	Spherical Face	M20	-	40.0	25	49	36	290	249
36401.W0162	Spherical Face	M24	-	46.0	20	49	41	498	258
36401.W0163	Spherical Face	M24	-	46.0	25	54	41	498	342
36401.W0164	Spherical Face	M24	-	46.0	30	59	41	498	398
36401.W0221	Ribbed Face	M 8	17	19.4	10	20	17	18	21
36401.W0231	Ribbed Face	M10	19	21.9	10	22	19	32	30
36401.W0232	Ribbed Face	M10	19	21.9	15	27	19	32	41
36401.W0201	Ribbed Face	M12	22	25.2	10	24	22	60	38
36401.W0202	Ribbed Face	M12	22	25.2	15	29	22	60	54
36401.W0242	Ribbed Face	M16	30	33.0	15	34	30	140	106
36401.W0243	Ribbed Face	M16	30	33.0	20	39	30	140	136



Order No.	Type	d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	A/F	Torque to Nm max.	Weight g
<b>36401.W0252</b>	Ribbed Face	M20	36	40.0	20	44	36	290	206
<b>36401.W0253</b>	Ribbed Face	M20	36	40.0	25	49	36	290	253
<b>36401.W0262</b>	Ribbed Face	M24	41	46.0	20	49	41	498	297
<b>36401.W0263</b>	Ribbed Face	M24	41	46.0	25	54	41	498	353
<b>36401.W0264</b>	Ribbed Face	M24	41	46.0	30	59	41	498	410

LOCATING PINS

