



# Screwed Rest Buttons - Plastic male thread

## Locating Pins



**36403**

LOCATING PINS

### Material

Body: stainless steel 1.4305  
Pad: plastic (PEEK), blue

### Technical Notes

The buttons are used as seats, stops,

supports and thrust pads in jigs and fixtures as well as machine and equipment design.  
Temperature range -60 to +250°C.

### Tips

For female thread see 36404.

| Order No.   | d <sub>1</sub> | d <sub>2</sub> | d <sub>3</sub> | h<br>±0.1 | l  | A/F <sub>1</sub> | A/F <sub>2</sub> | Static load<br>kN<br>max. | Tightening torque<br>Nm<br>max. | Weight<br>g |
|-------------|----------------|----------------|----------------|-----------|----|------------------|------------------|---------------------------|---------------------------------|-------------|
| 36403.W0122 | M 8            | 17.0           | 19.0           | 15        | 8  | 17               | 4                | 2.1                       | 10                              | 12          |
| 36403.W0133 | M10            | 19.0           | 21.5           | 20        | 10 | 19               | 5                | 2.4                       | 10                              | 18          |
| 36403.W0143 | M12            | 22.0           | 25.0           | 20        | 14 | 22               | 6                | 3.4                       | 10                              | 24          |
| 36403.W0021 | M 8            | 12.5           | 19.4           | 10        | 10 | 17               | -                | 2.8                       | 18                              | 15          |
| 36403.W0031 | M10            | 14.5           | 21.9           | 10        | 12 | 19               | -                | 3.8                       | 2                               | 21          |
| 36403.W0032 | M10            | 14.5           | 21.9           | 15        | 12 | 19               | -                | 3.8                       | 32                              | 33          |
| 36403.W0041 | M12            | 17.5           | 25.2           | 10        | 14 | 22               | -                | 5.5                       | 60                              | 30          |
| 36403.W0042 | M12            | 17.5           | 25.2           | 15        | 14 | 22               | -                | 5.5                       | 60                              | 46          |