



61345

ANTI-VIBRATION

Material

Rubber on yellow zinc plated steel (rubber hardness 45-65 Shore A).

for machines that move in three directions. Oil anti-drip hoods can be supplied on request.

air conditioners, ventilators and vibrating tables.

Technical Notes

The design of the mount makes them ideal

Tips

These mounts are found on compressors,

Order No.	Type	d ₁	d ₂	d ₃	h ₁	h ₂	l ₁	l ₂	Load kgf max.	Weight g
61345.W0450	Type 1	33.0	M 8	8.0	25	2.0	66	85	20	70
61345.W0451	Type 1	33.0	M 8	8.0	25	2.0	66	85	50	70
61345.W0650	Type 1	52.0	M10	10.5	35	2.5	92	114	40	170
61345.W0651	Type 1	66	M10	10.5	35	2.5	92	114	75	170
61345.W0850	Type 1	52.0	M10	11.5	40	3.0	110	136	75	303
61345.W0851	Type 1	52.0	M10	11.5	40	3.0	110	136	120	303
61345.W0900	Type 1	57.5	M10	12.5	45	3.0	125	150	130	430
61345.W0901	Type 1	57.5	M10	12.5	45	3.0	125	150	220	430
61345.W1300	Type 2	78.0	M12	14.5	63	5.0	120	150	280	1080
61345.W1301	Type 2	78.0	M12	14.5	63	5.0	120	150	500	1080
61345.W1700	Type 2	100	M16	14.5	84	4.0	160	200	380	2390
61345.W1701	Type 2	100	M16	14.5	84	4.0	160	200	750	2390
61345.W2500	Type 2	187	M24	18.5	158	6.0	250	310	1400	10400
61345.W2501	Type 2	187	M24	18.5	158	6.0	250	310	2500	10400



Recommendations for machine mounts

Machine mounts should be installed between two parallel and perfectly flat surfaces. Mounts operating tilted or twisted do not work properly. This may be due to incorrect alignment, tolerances in the building of the structure or over-tightened torque during the installation of the anti-vibration mounts.

ANTI-VIBRATION

