



## 36560

CLAMP CLEATS

### Material

Stainless steel (A4, AISI316, DIN 1.4401), with nylon insert.

Supplied with A2 (AISI303) stainless steel screw (screws not supplied with P1092.019, .020, or .026).

### Technical Notes

Quick release, faster clamping and self-locking.

### Tips

Bolt circle: use the larger of the following two bolt circles:

add 6,86 to max. flange diameter or add 10,16 to max. groove base diameter.

| Order No.   | $h_1$<br>$\pm 6,08$ | $d_1$ | $h_2$<br>$\pm 0,08$ | $h_3$ | $h_4$ | $l_1$<br>$+0 -0.8$ | $w_1$ | $w_2$<br>$+0 -0.15$ |
|-------------|---------------------|-------|---------------------|-------|-------|--------------------|-------|---------------------|
| 36560.W0006 | 0.79                | M3    | 1.02                | 1.80  | 1.73  | 8.0                | 9.90  | 3.18                |
| 36560.W0007 | 1.57                | M3    | 1.02                | 2.59  | 1.73  | 8.0                | 9.90  | 3.18                |
| 36560.W0008 | 1.58                | M3    | 1.27                | 2.84  | 1.73  | 10.0               | 9.90  | 3.18                |
| 36560.W0009 | 1.57                | M3    | 1.60                | 3.18  | 1.73  | 10.0               | 9.90  | 3.18                |
| 36560.W0010 | 1.98                | M3    | 1.60                | 3.58  | 1.73  | 10.0               | 9.90  | 3.18                |
| 36560.W0011 | 2.36                | M3    | 1.02                | 3.38  | 1.73  | 10.0               | 9.90  | 3.18                |
| 36560.W0012 | 2.36                | M3    | 1.27                | 3.63  | 1.73  | 10.0               | 9.90  | 3.18                |
| 36560.W0013 | 2.36                | M3    | 1.60                | 3.96  | 1.73  | 10.0               | 9.90  | 3.18                |
| 36560.W0014 | 3.18                | M3    | 1.27                | 4.45  | 1.73  | 10.0               | 9.90  | 3.18                |
| 36560.W0015 | 3.96                | M3    | 1.02                | 4.98  | 1.73  | 10.0               | 9.90  | 3.18                |
| 36560.W0016 | 5.72                | M3    | 1.60                | 7.32  | 1.73  | 12.0               | 9.90  | 3.18                |
| 36560.W0017 | 6.35                | M3    | 1.60                | 7.92  | 1.73  | 16.0               | 9.90  | 3.18                |