


Anti-vibration Mounts rectangular





61470

Material

Rubber on silver zinc plated steel (rubber hardness - 55 Shore A).

Technical Notes

Used where transverse loads are present.

Order No.	Type	d_1	I ₁	h_1	l ₂	l ₃	I ₄	w_1	w_2	Compression max.	Static load kgf max.
61470.W0100	Type 1	13	100	20	-	-	-	130	-	2	850
61470.W0150	Type 2	13	150	23	215	185	15	145	60	2	1300
61470.W0200	Type 2	13	200	23	265	235	15	145	60	2	1700





Recommendations for machine mounts

Machine mounts should be installed between two parallel and perfectly flat surfaces. Mounts operating tilted or twisted do not work properly. This may be due to incorrect alignment, tolerances in the building of the structure or over-tightened torque during the installation of the anti-vibration mounts.

