





# Anti vibration Mounts v shaped v shaped

## Anti-Vibration



**61510**

ANTI-VIBRATION

**Material**

Rubber on silver zinc plated steel (rubber hardness 45-65 Shore A).

and one to the piece of equipment. Very good as a shock/isolating mount for oscillations higher than 15Hz.

and air conditioning units from the wall.


**Technical Notes**

Has a three point anchorage, two to a base

**Tips**

Can be used to hang compressors, speakers

Order No.	Shore hardness	d <sub>1</sub>	Compression max.	h <sub>1</sub>	h <sub>2</sub>	l <sub>1</sub>	w <sub>1</sub>	l <sub>2</sub>	Axial load kgf max.	Radial load kgf max.
61510.W0045	45	12	2.5	35	3	90	73	112	60	60
61510.W0055	55	12	3.5	35	3	90	73	112	65	65
61510.W0065	65	12	6.0	35	3	90	73	112	70	70



### Recommendations for machine mounts

Machine mounts should be installed between two parallel and perfectly flat surfaces. Mounts operating tilted or twisted do not work properly. This may be due to incorrect alignment, tolerances in the building of the structure or over-tightened torque during the installation of the anti-vibration mounts.

ANTI-VIBRATION

