


Clamping Levers welded

Clamping Levers



73920

CLAMPING LEVERS

Material

Case hardened steel, or stainless steel AISI 303. Shaft butt welded.

Technical Notes

Low price version to no. 74200.

Order No.	Finish	d ₁	d ₂	d ₃	h ₁	h ₂ ≈	l ₁	l ₂ ≈	Weight g
73920.W0506	Steel	M 8	16	10	12.5	30.5	63	60	39
73920.W0508	Steel	M10	20	12	15.0	37.0	80	76	74
73920.W0510	Steel	M12	25	14	19.0	46.0	100	95	149
73920.W0512	Steel	M16	32	18	25.0	58.5	125	119	316
73920.W0516	Steel	M20	40	20	31.0	73.0	160	152	533
73920.W0606	Stainless Steel	M 8	16	10	12.5	30.5	63	60	39
73920.W0608	Stainless Steel	M10	20	12	15.0	37.0	80	76	73
73920.W0610	Stainless Steel	M12	25	14	19.0	46.0	100	95	153
73920.W0612	Stainless Steel	M16	32	18	25.0	58.5	125	119	314
73920.W0616	Stainless Steel	M20	40	20	31.0	73.0	160	152	533