





74201

CLAMPING LEVERS

Material

Stainless steel 1.4305 (AISI 303), dull blasted.

Order No.	Finish	a	b ≈	d ₁	d ₂ tol. H7	d ₂	d ₃	h ≈	l ₁	l ₂ ≈	Weight g
74201.W0206	Smooth Bore	5.0	12.0	10	8	-	16	30.5	63	60	37
74201.W0208	Smooth Bore	6.0	14.5	13	10	-	20	38.0	80	76	73
74201.W0210	Smooth Bore	7.5	18.5	16	12	-	25	47.0	100	95	140
74201.W0405	Threaded Bore	4.0	9.5	8	-	M_6	12	24.0	50	48	17
74201.W0406	Threaded Bore	5.0	12.5	10	-	M_8	16	30.5	63	60	38
74201.W0408	Threaded Bore	6.0	15.0	13	-	M10	20	38.0	80	76	74
74201.W0410	Threaded Bore	7.5	19.0	16	-	M12	25	47.0	100	95	142
74201.W0412	Threaded Bore	10.0	25.0	20	-	M16	32	59.5	125	119	297